



Philips PicoPix
Pocket projector

30 lumens
with USBQuickLink

PicoPix



PPX2330

Project your life

The PicoPix pocket projector with USB QuickLink offers a USB plug and socket for direct connection to a wide range of appliances to project your digital content onto a screen up to 60" in size.

Bright and colourful image

- LED technology for brilliant colours and high contrast

USBQuickLink

- USB plug and socket for power and easy connection

Ultra portable

- Play videos directly from your USB-Stick or internal memory

Direct video connection

- Share videos right from your mobile devices
- Share your Notebook screen simply via USB connection

PHILIPS

Specifications

Technology/optical

- Display technology: DLP
- Light source: RGB LED
- LED light source lasts over: 30.000 hours
- Brightness: up to 30 lumens
- Native resolution: 640 x 360 pixels
- Contrast ratio: 1500:1
- Colour temperature: 6500 Kelvin
- Throw ratio: 1.6:1
- Screen size (diagonal): 25.4 cm–152.4 cm
- Screen distance: 0.354 m–2.125 m
- Focus: manual
- Internal memory: 2 GB
- Integrated MP4 player
- Direct link to smartphone: via USB

Supported video standards

- PAL
- SECAM
- NTSC

Sound

- Internal speaker: 1 W

Connection

- Output audio: 3.5 mm audio out jack for headphones
- External Memory: micro SD/SDHC
- USB: slave — mass storage device (x-change data with PC); slave — video streaming; master — connect mass storage device; charging
- AV in: share the jack with audio out

Internal media player

- Supported video formats: .avi: MPEG-4; H.264; M-JPEG/.mov: MPEG-4; H.264/.mp4: MPEG-4; H.264/.mkv: MPEG-4; H.264; M-JPEG/.ts: H.264/.rm: RV3;

RV4/.rmvb: RV3; RV4

- Supported audio formats: MP3, WAV
- Supported photo formats: JPEG, BMP

Power Supply

- Battery life: Standard mode: 2 hours; Bright mode: 1.5 hours; LED indicator: battery charge
- Internal battery: 3.7 V @ 2600 mAh

Dimensions

- Packed (W x D x H): 130 x 90 x 70 mm
- Unpacked: 96.7 x 54 x 22 mm

Weight

- Packed: 246 g
- Unpacked: 0.130 kg

Temperature range

- Operation: 5–40° C
- Storage packed: -25–60° C
- Storage unpacked: 0–45° C

Relative humidity

- Operation: 15–85% RH
- Storage packed: 5–93% RH
- Storage unpacked: 15–85% RH

Standard package includes

- User guide: on internal memory, Internet
- Warranty card
- Carrying case
- Quick start guide
- PPX2330

Accessories

- PPA6200 power adapter 5 V/2 A: optional

Highlights

LED-Technology

Your pictures and videos deserve the best quality when it comes to sharing them with those around you. This is why the PicoPix pocket projector uses high quality LED technology to project your pictures and videos in brilliant colours and breathtaking contrast.

Direct Video connection

Connect your mobile devices and project all your content directly with your PicoPix on a big screen.

Integrated MP4 Media player

The integrated MP4 Media player supports all common video and audio formats. This makes the PicoPix pocket projector a standalone device, retrieving its content from the internal 2 GB memory, USB stick or a micro SD card.

USBQuickLink

For those who want to share content directly from their camera, smartphone or USB Stick, the USBQuickLink is the easiest connection to all these devices. When on-the-go, just stick the USB plug and socket together and use the USBQuickLink as a handle.

Video Streaming

Share your Notebook screen showing your Media- or Web content, like YouTube videos or Party pics, with those around you. Just connect your PicoPix to the PC or Notebook via USB and start projecting.



Issue date 2018-12-04

Version: 2.1.1

12 NC: 8670 000 92396
EAN: 34 25160 30801 3

© 2018 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com