




Philips
In-ear headphones with
mic

8.6mm drivers/closed-back

integrated mic
Black
In Ear



PRO6105BK

Perfectly clear

When clear sound is all you need. From playlist to podcast to call, these wired in-ear headphones get it right. They're also Hi-Res Audio compatible: if you're listening to your favorite high-resolution streaming service, you'll hear more.

Clear sound. Perfect fit.

- 9 mm neodymium acoustic drivers
- Clear sound. Punchy bass

From focus playlist to vital call

- Passive noise isolation. Be immersed
- Hi-Res Audio. Hear more
- Built-in mic with echo cancellation for clear audio

Feels good. Looks good.

- Oval acoustic tube. Comfort and passive noise isolation
- 3 interchangeable rubber earbud covers. Comfortable fit
- Carry pouch. Keep them safe when they're not on

PHILIPS

In-ear headphones with mic
8.6mm drivers/closed-back integrated mic, Black, In Ear

Specifications

Sound

- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Speaker diameter: 8.6
- Sensitivity: 109 dB
- Diaphragm: Mylar dome
- Frequency response: 7-40,000 Hz

Connectivity

- Microphone: Microphone in 3.5 mm jack
- Finishing of connector: gold-plated
- Cable length: 1.2 m

Accessories

- Ear caps: Extra 2 pairs

Packaging dimensions

- Packaging type: Box
- Number of products included: 1
- Type of shelf placement: Hanging
- Packaging dimensions (W x H x D):
7 x 17.5 x 2.5 cm

- Gross weight: 0.05 kg
- Nett weight: 0.018 kg
- Tare weight: 0.032 kg
- EAN: 69 51613 98178 8

Outer Carton

- Number of consumer packagings: 24
- Outer carton (L x W x H): 38 x 18.3 x 19.6 cm
- Gross weight: 1.59 kg
- Nett weight: 0.432 kg
- Tare weight: 1.158 kg
- GTIN: 1 69 51613 98178 5

Inner Carton

- Number of consumer packagings: 3
- Inner carton (L x W x H): 18 x 8.2 x 7.8 cm
- Gross weight: 0.17 kg
- Nett weight: 0.054 kg
- Tare weight: 0.116 kg
- GTIN: 2 69 51613 98178 2

UPC

- UPC: 8 40063 20210 8

PRO6105BK/00

Highlights

From playlist to vital call

Take a call, pause your playlist. All without touching your smartphone. The built-in mic with echo cancellation keeps sound clear when you're talking. When you're listening to music and podcasts, perfectly tuned neodymium acoustic drivers deliver clear, detailed sound.

Hi-Res Audio. Hear more.

Love your high-resolution streaming service? Hear more with these Hi-Res Audio headphones. Capable of reproducing high frequencies of up to 40 kHz, they'll give you more detail when you're on the move.

Stay comfortable.

An oval acoustic tube and three sizes of interchangeable rubber earbud covers create a perfect seal. Enjoy all-day listening comfort and excellent passive noise isolation.

Oval acoustic tube

Oval acoustic tube. Comfort and passive noise isolation

9 mm neodymium drivers

9 mm neodymium acoustic drivers

Carry pouch.

Carry pouch. Keep them safe when they're not on

Clear sound. Punchy bass

Clear sound. Punchy bass

Passive noise isolation

Passive noise isolation. Be immersed



Issue date 2022-05-12

Version: 5.0.2

12 NC: 8670 001 58806
EAN: 69 51613 98178 8

© 2022 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com