

# MP3MAX

512 MB DIGITAL AUDIO PLAYER

type number - PSA250



The **MP3MAX** is pure solid-state which means no moving parts for 100% skip-free wearable sport audio.

Designed with athlete insights and technology innovations the product can be worn securely on the arm or around the waist. The five-key remote control waist belt provides the user with an easy to operate interface, secure fit and comfort on the move.

Featuring 250 songs\* of skip-free audio, and a FM radio with 10 station presets onboard, you'll never run out of new music to inspire your daily workouts.

Add a dedicated stopwatch, a state-of-the-art illumination technology strobe light that enhances the users visibility in low light conditions and you've got the ultimate wearable sport audio player that combines music, workout features and sport-tested durability.



INNOVATION FOR ATHLETES

**PHILIPS**

Running is encouraged.

Skipping is not.



# MP3 MAX

## 512 MB DIGITAL AUDIO PLAYER

type number - PSA250

### MAIN FEATURES

- > Wearable
- > Skip free audio
- > Stopwatch
- > Illumination technology
- > Sport tested durable

### PRODUCT HIGHLIGHTS

- > 512MB built-in memory\*\* - 16 hours of WMA or 8 hours of MP3 music [over 250 WMA or 125 MP3 songs]\*
- > Plays mp3, Windows media formatted content and future formats
- > FM radio with 10 presets
- > Remote control waist belt
- > Dedicated stopwatch
- > Strobe light for low light conditions
- > Backlit LCD display
- > 4 EQ presets and Dynamic Bass Boost
- > 12 hours playback time\*\*\*
- > 1 hour rapid [4 hours full] battery recharging time
- > Audio manager software included:  
Musicmatch Jukebox  
Philips Media Manager

### PRODUCT INFORMATION

#### SYSTEM REQUIREMENTS

USB port / CD-ROM drive / 256MB of RAM / 1GB Hard drive capacity

#### PC

300MHz processor or better  
Windows\* 98 SE, 2000, ME, XP

#### AMPLIFIER / SYSTEM

Output power (rms): 2 x 5mW  
Digital volume control  
S/N ratio [A weighted]: >80 db  
Frequency response: 20 Hz – 20 kHz  
FM frequency range: 87.5 – 108 MHz

#### DISPLAY

Graphical LCD

Displays track number, title, artist, time, genre, battery level, stopwatch time, FM frequency and preset station

#### CONNECTIONS

Headphone / line out: stereo, 3.5 mm  
I/O interface: 5 pin USB jack

#### POWER SUPPLY

Battery: rechargeable Li-Ion battery  
Battery Charging time: 1 hour rapid (4 hours full)  
Automatic power switch-off

#### GENERAL

Case material: plastic

Weight: 70 g

Product dimensions [mm]: 26,5 D x 71 W x 71 H

Package dimensions [mm]: 193 W x 193 L x 96,5 H

Master carton dimensions [mm]: 312 W x 203 L x 211 H

UPC: 87 10895 80875 0

UPC carton: 9073 101 01125

#### CONTENTS

- [A] Digital audio player [PSA250]
- [B] Sport headphones [SBC HJ030/77]
- [C] Waist belt remote control [AY4002]
- [D] Sport armband [AY4208]
- [E] USB cable [AY3912]
- [F] CD-ROM [AY4485]
- [G] AC / DC Adapter / Charger [AY4102]



[A]



[B]



[C]



[D]



[E]



[F]



[G]



NIKE



SWOOSH



PHILIPS

© 2004 Phillips, Nike, Inc. All rights reserved. Windows Media is a trademark of Microsoft Corporation. All other brand and product names are the trademarks of their respective companies or organizations.

\* 16 hours of WMA or 8 hours of MP3 music (over 250 WMA or 125 MP3 songs) \*\* Actual formatted capacity will be less  
\*\*\* Battery life varies with use

www.nike-philips.com