

Your perfect music companion at home and on the move.

Enjoy superb sound with powerful bass at home or away with the uniquely portable ShoqBox. Savour 60 MP3 or 120 WMA songs in dynamic sound with XSL Acoustics. Your ShoqBox with built-in speakers is small enough to carry or fit anywhere!

Powerful sound from a sleek design

- Enjoy MP3 and WMA playback
- Play secure WMA (DRM) songs from online music services
- Stores up to 8* hours of music (MP3 & WMA)
- Built-in speakers featuring XSL Acoustics for dynamic sound

Create your personal space anywhere

- Wake up to your own music or alarm
- More music with Digital FM Radio with 10 station presets

Freedom to listen to music anywhere

- Use as portable speakers for any music player or PC
- Enjoy up to 10-hour music playback**
- Built in rechargeable battery
- Travel case included



Technical specifications

Picture / Display

- **Backlight colour:** White
- **Indications:** battery status, DBB, time
- **Lines of text:** 5
- **Resolution:** 128 x 96 pixels
- **Type:** LCD

Sound

- **Equaliser settings:** Classic, Hip Hop, Jazz, Pop, Rock
- **Frequency response:** 20 - 20 000 Hz
- **Signal/noise ratio:** >80 dB (earphone), >50dB (speaker)
- **Sound enhancement:** Dynamic Bass Boost
- **Output power (RMS):** 2 x 2 W RMS (4 ohm, speakers), 2 x 3 mW RMS (16 ohm, headphones - note: HP not included)
- **Volume Control:** digital

Audio Playback

- **Compression format:** MP3, Windows Media (TM) Audio
- **ID3 tag support**
- **MP3 bit rates:** 8-320 kbps and VBR
- **MP3 sample rates:** 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz
- **WMA bit rates:** 5 - 192
- **WMA sample rates:** 8, 11.025, 16, 22.050, 32, 44.1, 48

Storage Media

- **Built-in memory capacity:** 256 MB
- **Built-in memory type:** NAND Flash
- Mass storage class compliant
- **Music memory capacity, MP3:** up to 60 (128kbps and four min.)
- **Music memory capacity, WMA:** up to 120 (64kbps and four min.)

Tuner / Reception / Transmission

- **Frequency range:** 87.5 - 108 MHz
- **Station presets:** 10
- **Tuner bands:** FM stereo

Connectivity

- **Aux in:** Line-in, 3.5 mm
- **Cables:** Line-in cable (AY3485)
- **DC in:** 5 V, D=3.0 mm
- **Headphone:** 3.5 mm
- **USB:** USB 1.1

Accessories

- **AC/DC adaptor/charger:** multi-voltage, AC:100-240 V, 50-60 Hz, DC: 5 V (AY3192)
- **Cables:** Line-in (AY3485)
- **CD-ROM:** (AY4493): Device Manager, Musicmatch Jukebox, user manuals.
- **Pouch:** Travel case (AY4218)
- **USB cable:** (AY3841)

Green Specifications

- Lead-free soldered product

System Requirements

- CD-ROM drive
- **Hard disc space:** 50 MB
- **PC OS:** Windows 98 SE, 2000, ME, XP
- **RAM memory:** 96 MB RAM
- **USB:** Free USB port

Dimensions

- **Outer carton dimensions WxDxH:** 268 x 204 x 248 mm
- **Master carton quantity:** 2
- **Packaging dimensions (W x H x D):** 230 mm x 256 mm x 96 mm
- **Packaging type:** D-box
- **Product dimensions (WxDxH):** 58 x 53 x 182 mm
- **Product weight:** 0.350 kg

Power

- **Adaptor type:** multi-voltage (AC: 100 - 240 V, 50 - 60 Hz)
- **Battery capacity:** 1600 mAh
- **Battery type:** Li-ion
- **Charging time:** 4 hr
- **Playtime on internal battery:** Up to 10 hours
- Rechargeable

Product highlights

Use as portable speakers

You want dynamic sound and powerful bass output from tiny speakers to liven up your listening experience! Your ShoqBox features a pair of tiny yet powerful speakers that deliver powerful bass with sound big enough to fill a room. Connect the cable from the line-out or headphone port of your audio source to the line-in port of the ShoqBox. Then select the line-in function from the main menu of your ShoqBox. Bring your presentations to life or sit back and enjoy big sounds.

XSL Acoustics

Enjoy dynamic sound and powerful bass performance from your ShoqBox with XSL Acoustics. Impressive sound is produced by combining bright, brisk treble and mid range sound with elastic, powerful bass. Innovative use of high-tech materials like titanium cone and neodymium magnet deliver sound output that's nearly double the power of a traditional speaker driver of the same size. Precise tuning between the speaker driver, the small acoustic architecture and the circuitry ensures superbly dynamic sound and optimises bass performance from the smallest sound enclosure.



Date of issue 2005-12-16

Version: 6.0

12 NC: 9073 101 01664
EAN: 87 10895 85848 9

Specifications are subject to change without notice.

Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

© 2005 Koninklijke Philips Electronics N.V.

All Rights reserved.

www.philips.com

- 1MB = 1 million bytes; available storage capacity will be less.
- Rechargeable batteries have a limited number of charge cycles and may eventually need to be replaced. Battery life and number of charge cycles vary by use and settings.
- Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.
- Windows Media and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.