

ShoqBox

PSS110

Your perfect music companion at home and on the go

Enjoy superb sound with powerful bass at home or away with the uniquely portable ShoqBox. Savor 60 MP3 or 120 WMA songs in dynamic sound with XSL Acoustics. Your ShoqBox with built-in speakers is small enough to carry or fit anywhere!

Powerful sound from a sleek design

- Enjoy MP3 and WMA playback
- Play secure WMA (DRM) songs from online music services
- Stores up to 8 hours* of music
- Built-in speakers featuring XSL Acoustics for dynamic sound

Create your personal space anywhere

- Wake up to your own music or alarm
- More music with Digital FM Radio with 10 station presets

Freedom to listen to music anywhere

- Use as portable speakers for any music player or PC
- Enjoy up to 10-hour music playback**
- Built-in rechargeable battery
- Travel case included



GoGear

PHILIPS

Technical specifications

Picture / Display

- Display Type: LCD
- Backlight: White superbright LED
- Line of text: 5
- Resolution: 128 x 96 pixels
- Indication: Battery status, time, alarm, DBB,
- Language support: English, French, Spanish, German, Dutch, Danish, Swedish, Finnish, Norwegian, Italian, Portuguese, Turkish

Sound

- Output power:
 - 2 x 2 W RMS (4 ohm, speaker)
 - 2 x 3 mW RMS (16 ohm, earphone)
- Amplifier:
 - 2 ch x 2 W Class-D amplifier
- Sound enhancement technology:
 - Dynamic Bass Boost (DBB)
- Equalizer: 6 bands
- Equalizer settings: Rock, Pop, Jazz, Hiphop, Classic, Normal
- Volume control: Digital
- Signal to noise ratio: >80 dB (earphone), >50 dB (speaker)
- Frequency response: 20 Hz-20 KHz

Audio Playback

- Compression format: MP3, WMA
- ID3 Tag support: Track titel, artist name, album name, file name
- MP3 bit rates: 8-320 kbps and VBR
- MP3 sample rates:
 - 8, 11.025, 16, 22.050, 32, 44.1, 48 KHz
- WMA bit rates: 5-192 kbps
- WMA sample rates:
 - 8, 11.025, 16, 22.050, 32, 44.1, 48 KHz

Storage Media

- Built-in memory capacity: 256 MB*
- Built-in memory type: NAND Flash
- Mass storage class compliant
- Music memory capacity (MP3):
 - Up to 60 tracks (128 kbps)*
- Music memory capacity (WMA):
 - Up to 120 tracks (64 kbps)*

Tuner / Reception

- Frequency range: 87.5-108 MHz
- Station presets: 10
- Tuner bands: FM Stereo

Connectivity

- DC in: 5 V, D=3.0 mm
- Headphone: 3.5 mm
- USB: type B port, 5P, USB 1.1
- Line in (Aux in): 3.5 mm
- FM antenna: 3.5 mm

Convenience

- Firmware upgradeable

Accessories

- AC/DC adaptor/charger: multi-voltage, AC: 100-240 v, 50-60 HZ, DC: 5 V (AY3192)
- USB cable (AY3841)
- Line-in cable (AY3485)
- CD-ROM (AY4493): Device Manager, Musicmatch Jukebox, user manuals
- FM antenna (AY3486)
- Travel case (AY4218)

Green Specification

- Lead-free soldered product

Dimensions

- Master carton quantity: 3
- Packaging dimensions (WxHxD):
 - Approx. 8.4 x 12.0 x 3.3 inch
- Packaging type: Clamshell
- Product dimensions (WxHxD):
 - 2.28 x 2.09 x 7.17 inch
- Product weight: 12.35 oz

Power

- Adaptor type: multi-voltage (AC: 100-240 V, 50-60 HZ)
- Battery type: built-in Li-ion rechargeable battery
- Battery capacity: 1600 mAh
- Battery playback time: 10 hours**
- Charging time: 4 hours
- Battery replaceable: by Philips service only

System requirements

- PC OS: Windows 98SE/ME/2000/XP
- USB port
- CD-ROM drive
- Hard disc space: 50 MB
- Processor: Pentium MMX 166 MHz processor or better
- RAM memory: 96 MB

UPC: 0 37849 95597 0 (/17)

Date of issue 2005-04-19

Specifications are subject to change without notice.

Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.

© 2005 Koninklijke Philips Electronics N.V.

All rights reserved.

www.philips.com

Product highlights

XSL Acoustics

Enjoy dynamic sound and powerful bass performance from your ShoqBox with XSL Acoustics. Impressive sound is produced by combining bright, brisk treble and mid range sound with elastic, powerful bass. Innovative use of high-tech materials like titanium cone and neodymium magnet deliver sound output that's nearly double the power of a traditional speaker driver of the same size. Precise tuning between the speaker driver, the small acoustic architecture and the circuitry ensures superbly dynamic sound and optimizes bass performance from the smallest sound enclosure.

Portable speakers on the go

You want dynamic sound and powerful bass output from tiny speakers to liven up your listening experience! Your ShoqBox features a pair of tiny yet powerful speakers that deliver powerful bass with sound big enough to fill a room. Connect the cable from the line-out or headphone port of your audio source to the line-in port of the ShoqBox. Then select the line-in function from the main menu of your ShoqBox. Bring your presentations to life or sit back and enjoy big sounds.

6-Mode equalizer

Equalizer allows you to select preset modes that optimize certain frequency bands to enhance specific music styles. Players with Equalizer, utilize graphic equalizing technology to automatically set the optimum sound frequency balance for a chosen music style. The Equalizer allows you to enjoy the optimum sound depending on the music style.

Firmware upgradeable

Stay up to date with the latest firmware upgrades from Philips. Improvements such as new features, functions and media formats are made available constantly to provide you the best experience with Philips products. Philips online support site easily provides automatic and timely updates via email. So you can easily search and download new firmware releases to update your product with new features, functions and media formats. Download the latest upgrades from www.philips.com/support and upgrade your player with latest firmware.

Digital tuner

Digital tuner memorizes up to 10 tuner presets or delivers the 'best 10' FM stations based on reception quality. Digital tuner scans through frequencies and locks on to each station located. Allocate a preset number to your favorite stations and easily return to those stations time and again without having to remember radio frequencies.

* Available storage capacity will be less. Capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.

** Battery life varies with use

Windows Media and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

