


PHILIPS

dry electric shaver

PowerTouch Plus

DualPrecision blades

Pivoting heads



PT870



A closer, cleaner shave

The new Philips PowerTouch system adds power to your morning. Now with more minutes, full washability and proven DualPrecision shaving performance, PowerTouch ensures that you are always ready to quickly finish your morning routine.

The fastest way through your morning routine

- 50+ minutes of cordless shaving, 1 hour charge
- Washable shaver with QuickRinse system

A comfortable and close end result

- Super Lift & Cut system for a comfortably close shave
- Dynamic contour response adjusts to face and neck curves
- DualPrecision cutting shaves even the shortest stubble
- SmartPivot maintains constant skin contact
- Pop up trimmer perfect for sideburns and moustache

Highlights

Efficient Power System:50+ min



50+ minutes of cordless power for 17 shaves. Fully charges in 1 hour so it is always ready when you are

Super Lift&Cut Action

The dual blade system built into our electric shaver lifts hairs to cut comfortably below skin level for a closer shave

Dynamic contour response

Automatically adjusts to every curve of your face and neck for a smoother shave

DualPrecision Cutting

DualPrecision shaving heads have slots to shave the normal hairs and holes to shave even the shortest stubble

Fully washable shaver




Fully washable shaver with QuickRinse system rinses clean in less time

SmartPivot



Constantly keeps the 3 shaving heads in close contact with your skin for a fast shave

Pop up trimmer



The full width, pop-up trimmer is perfect for grooming your sideburns and moustache

Specifications

Shaving Performance

Shaving System: DualPrecision cutting, Super Lift&Cut

Contour-following: SmartPivot, Dynamic contour response

Styling: Integrated pop up trimmer

Ease of use

Shaving time: 50+ minutes

Charging: Rechargeable, Cordless & corded operation, Quick charge 3 min for 1 shave

Charging time: 1 hour

Display: 2 LED indication, Charging indication, Battery low indication, Battery full indication, Quick charge indication

Cleaning: Fully washable shaver, Quick rinse hair chamber

Design

Handle: Easy grip, Ribbed rubber grip

Finishing: Front Shell (lacquered), Lacquered deco ring, Mirror black display panel

Color: Dark metal inox

Accessories

Maintenance: Cleaning brush, Protection cap

Power

Battery type: Li-Ion

Automatic voltage: 100-240 V

Stand-by power: < 0.2 W

Max power consumption: 5.4 W

Service

2-year guarantee

Replacement head: Replace every 2 yrs with HQ8

