

PHILIPS

NORELCO

electric razor

PowerTouch

Plus



PT870



A closer, cleaner shave

The new Philips PowerTouch system adds power to your morning. Now with more minutes, full washability and proven DualPrecision shaving performance, PowerTouch ensures that you are always ready to quickly finish your morning routine.



The fastest way through your morning routine

- 50+ minutes of cordless shaving, 1 hour charge
- Washable razor with QuickRinse system

A comfortable and close end result

- Super Lift & Cut system for a comfortably close shave
- Dynamic contour response adjusts to curves in the face and neck
- DualPrecision cutting shaves even the shortest stubble
- SmartPivot maintains constant skin contact
- Pop-up trimmer perfect for sideburns and moustaches

Highlights

Efficient Power System: 50+ min



50+ minutes of cordless power for 17 shaves. Fully charges in 1 hour so it is always ready when you are

Super Lift&Cut Action



The dual blade system built into our electric razor lifts hairs to cut comfortably below skin level for a closer shave

Dynamic contour response



Automatically adjusts to every curve of your face and neck for a smoother shave

DualPrecision Cutting



DualPrecision shaving heads have slots to shave the normal hairs and holes to shave even the shortest stubble

Fully washable razor



Fully washable razor with QuickRinse system rinses clean in less time

SmartPivot



Constantly keeps the 3 shaving heads in close contact with your skin for a fast shave

Pop-up trimmer



The full width, pop-up trimmer is perfect for grooming your sideburns and moustache

Specifications

Shaving Performance

Shaving System: DualPrecision cutting, Super Lift&Cut

Contour-following: SmartPivot, Dynamic contour response

Styling: Integrated pop-up trimmer

Ease of use

Shaving time: 50+ minutes

Charging: Rechargeable, Cordless & corded operation, Quick charge 3 min for 1 shave

Charging time: 1 hour

Display: 2 LED indication, Charging indication,

Battery low indication, Battery full indication, Quick charge indication

Cleaning: Fully washable razor, Quick rinse hair chamber

Design

Handle: Easy grip, Ribbed rubber grip

Finishing: Front Shell (lacquered), Lacquered deco ring, Mirror black display panel

Colour: Dark metal inox

Accessories

Maintenance: Cleaning brush, Protection cap

Power

Battery type: Li-Ion

Automatic voltage: 100-240 V

Stand-by power: < 0.2 W

Max power consumption: 5.4 W

Service

2-year guarantee

Replacement head: Replace every yr with HQ8

