

PHILIPS

Upright bike

ReCare



PTE7000MU



Builds lower-body strength and conditioning

Designed with comfort

Patients can enjoy the oversized, padded seat with precise positioning for a comfortable ride. Adjustable crank lengths for limited ranges of motion, METs measurements and downloadable workout data help clinicians provide better aid to users.

Custom fit for function

- Adjust crank length to fit range of motion
- Adjust the seat up, down, forwards or backwards

Innovative programmes

- The console displays workout data
- Console measures strength input on left and right sides

User friendly

- The console features an easy-to-read display
- Numbered seat and pedal adjustments are available

Highlights

Console



The console displays essential, real-time patient performance feedback. Patient data can be streamed at the same time. Windows display time, rotations per minute, watts, calories, METs, heart rate and power.

Console



Large, bright LED windows make it easy for users and clinicians to monitor important workout data at a glance.

Crank adjustment



To help patients with limited mobility or injuries, the pedals can be moved along the crank to accommodate a range of motion as

small as 15 degrees. Smaller degrees render smaller circular lower-body motions, so that patients can complete a full 360 degree stroke during rehabilitation. Cranks are indexed for keeping track of how far you have improved, as well as for precise repetition.

Indexed adjustments



By documenting numbered adjustments, patients can quickly and easily set up the bike with indexed seat distance and crank settings.

Seat adjustment



For the best body positioning and comfort, the seat adjusts vertically and horizontally and is secured via locking pop-pins. Settings are indexed for consistent setup for each workout.

Symmetry programme

The symmetry programme allows clinicians to measure improvement for patients who are working on strengthening a weaker leg.

Specifications

Compliance

Certifications: CAN/CSA-C22.2 No. 60601-1:14, ANSI/AAMI, ES60601-1:2005+A2 (R2012) +A1, IEC 60601-1-2:2014, EN 60601-1-2:2015, IEC 60601-1:2015+A1:2012, EN 60601-1:2006, +A1:2013, +A12:2014, EN ISO 20957:2013, MDD 93/42/EEC Class Im., NB: 0123

Max. user weight

lbs: 440
kg: 200

Net weight

lbs: 142.2
kg: 65

Overall dimensions

inches: 47.7 x 25 x 55
cm: 121 x 64 x 140

Power AC

Volts: AC 100-240 V

Drive train

Heavy-duty: 8-groove poly-V belt, with spring-loaded idlers

CSAFE

Yes: -

Hand pulse

Yes: -

Programmes

include: Custom, Hill, HR, Interval profiles, Isokinetic, Manual, Plateau, Symmetry, VO2

Resistance

level: 1 to 50
type: Magnetic resistance system

Start resistance

watts: 5

Work range

watts: 5 to 750

