

PHILIPS

Hair clipper plus

With contour following comb



QC5335



Maximum precision, minimum effort

Advanced contour following system

Effortless precision for a comfortable and even hair cut

Maximum precision

- Advanced contour-following comb for speed and comfort
- Skin-friendly blades and combs are gentle to the skin
- High precision: 20 lock-in precision length settings

Minimum effort

- Adjustable guide combs for extra convenience
- Efficient Power System: 8hrs/45 minutes
- Corded and cordless use
- Battery charging, full and low indication
- Self-sharpening blades
- Lubrication for life
- Product comes in a luxury case for storage and protection

Highlights

Contour-following comb



The 2D combs gently follow the contours of your head for a smooth, even and comfortable hair cut.

Efficient Power System



The battery is fully charged in 8 hour and provides power for up to 45 minutes cordless use.

Self-sharpening blades




The self-sharpening, stainless steel blades stay sharp longer and ensure top cutting performance.

Skin friendly



The rounded edges on the blades and combs are designed to avoid scratching the skin for a more comfortable experience.

Corded and cordless use



For flexibility and convenience the headroom can be used with or without the power cord.

Lubrication for life



No need for oil maintenance.

Adjustable guide combs



Easily select and set your desired hair length without the hassle of having to change attachments.

Battery indicator



A light display flashes white to indicate that the battery is charging and turns constant when it is fully charged.

Luxury storage case



Safely keep together your product and accessories in its luxury case. Includes a styling comb, scissors and a cleaning brush.

Range of 20 length settings

2 combs provide a full range of 20 length settings ranging from 3 to 41mm with a precision of 2 mm between each step up.

Specifications

Cutting system

Cutter width: 41 mm

Number of length settings: 20

Range of length settings: 3-41 mm

Precision (size of steps): by 2 mm

Self-sharpening stainless steel blades

Maintenance free - No Oil needed

Ease of use

Display: Charging indicator

Adjustable guide combs

Power system

Battery type: NiMH

Charging time: 8 hours

Running time: 45 minutes

Design

Easy grip: Side panels

Shape: Ergonomic

Accessories

Cleaning brush

Barber tools: Styling comb & scissors

Luxury case

Service

2-year worldwide guarantee

