

PHILIPS

NORELCO

Hair clipper pro

With contour following comb



QC5340/40



Maximum precision, minimum effort

Advanced contour following system

This rechargeable Philips Norelco hair clipper has a patented zoom ring to ensure easy length setting. The extra precision, the advanced contour-following comb and lithium-ion battery guaranty a faster and more comfortable experience.

Maximum precision

- Advanced contour-following comb for speed and comfort
- Skin-friendly blades and combs are gentle to the skin
- Professional precision: 40 lock-in precision length settings

Minimum effort

- Adjustable guide combs for extra convenience
- 100% washable for easy cleaning
- Quick Charge Power System: 1hr/60 minutes cordless use
- Corded and cordless use
- Battery charging, full and low indication
- Self-sharpening blades
- Lubrication for life

Highlights

Contour-following comb



The 2D combs gently follow the contours of your head for a smooth, even and comfortable hair cut.

Skin friendly



The rounded edges on the blades of your Philips hair clipper and combs are designed to avoid scratching the skin for a more comfortable experience.

Adjustable guide combs



Easily select and set your desired hair length without the hassle of having to change attachments.

100% washable




Wash the Philips hair clipper conveniently under the tap for a thorough clean.

Quick charge battery

The lithium-Ion battery is fully charged in 1 hour and provides constant power for up to 60 minutes cordless use.

Corded and cordless use



For flexibility and convenience the headroom can be used with or without the power cord.

Battery indicator



A light display flashes white to indicate that the battery is charging and turns constant when it is fully charged.

Self-sharpening blades



The self-sharpening, stainless steel blades stay sharp longer and ensure top cutting performance.

Lubrication for life



No need for oil maintenance.

Range of 40 length settings

2 combs provide a full range of 40 length settings ranging from 3 to 40 with a precision of 1mm between each step up.

Specifications

Cutting system

Cutter width: 41 mm

Number of length settings: 40

Range of length settings: 3-42 mm

Precision (size of steps): by 1 mm

Self-sharpening stainless steel blades

Maintenance free - No Oil needed

Ease of use

Zoomring: Easily adjust length settings

Display: Charging indicator

Power system

Battery type: Li-ion

Charging time: 1 hour

Running time: 60 minutes

Design

Easy grip: Side panels

Shape: Ergonomic

Accessories

Cleaning brush

Service

2-year worldwide guarantee

