

# PHILIPS

## NORELCO

Hair clipper pro

Professional power



QC5345/40



## Professional power

### Cuts even the thickest hair

This powerful Philips Norelco hair clipper cuts even the thickest hair, thanks to its ultra sharp blades and the most powerful lithium-ion battery on the market. One quick charge provides enough power for 75 minutes of cordless use.

#### Cuts even the thickest hair

- The most powerful battery on the market

#### Maximum precision

- Advanced contour-following comb for speed and comfort
- Skin-friendly blades and combs are gentle to the skin
- High precision: 20 lock-in precision length settings

#### Minimum effort

- Adjustable guide combs for extra convenience
- 100% washable for easy cleaning
- Corded and cordless use
- Battery charging, full and low indication
- Self-sharpening blades
- Lubrication for life

# Highlights

## Maximum power

The lithium-Ion battery is fully charged in 1 hour and provides constant power for up to 75 minutes cordless use.

## Contour-following comb



The 2D combs gently follow the contours of your head for a smooth, even and comfortable hair cut.

## Skin friendly

The rounded edges on the blades of your Philips hair clipper and combs are designed to avoid scratching the skin for a more comfortable experience.

## Adjustable guide combs




Easily select and set your desired hair length without the hassle of having to change attachments.

## 100% washable



Wash the Philips hair clipper conveniently under the tap for a thorough clean.

## Corded and cordless use



For flexibility and convenience the headroom can be used with or without the power cord.

## Battery indicator



A light display flashes white to indicate that the battery is charging and turns constant when it is fully charged.

## Self-sharpening blades



The self-sharpening, stainless steel blades stay sharp longer and ensure top cutting performance.

## Lubrication for life



No need for oil maintenance.

## Range of 20 length settings

2 combs provide a full range of 20 length settings ranging from 3 to 41mm with a precision of 2 mm between each step up.

# Specifications

## Cutting system

Cutter width: 41 mm

Number of length settings: 20

Range of length settings: 3-41 mm

Precision (size of steps): By 2mm mm

Self-sharpening stainless steel blades

Maintenance free - No Oil needed

## Ease of use

Display: Charging indicator

Adjustable guide combs

## Power system

Battery type: Li-ion

Charging time: 1 hour

Running time: 75 minutes

## Design

Finishing: Metal chrome plate

Shape: Ergonomic

Easy grip: Side panels

## Accessories

Cleaning brush

## Service

2-year worldwide guarantee

