

PHILIPS

do-it-yourself hair clipper

Stainless steel blades

8 length settings

Corded use



QC5510/15



Cut your own hair – even in hard-to-reach areas with the 180° rotating head

A perfectly smooth and precisely shaved head with the Philips do-it-yourself Headgroom

Easy to use

- Pop-open head makes it easy to clean with the included brush
- Corded use only
- 2-year guarantee, worldwide voltage.

Performance

- Easy to select and lock in 8 length settings from 3 mm to 15 mm
- High-performance trimmer with self-sharpening blades

Skin friendly


- Rounded tips and combs prevent skin irritation

Do it yourself

- 180° rotating head for easy reach
- Contour-following comb follows every curve of your head.

Highlights

180° rotating head



Makes trimming your own hair easier than ever. Simply select the best angle to comfortably reach all parts of your head without any assistance.

8 locking length settings

Turn the wheel to simply select and lock in the length setting you want. The adjustable comb provides length settings from 3 mm to 15 mm, with precisely 2 mm between each length. You can also use it without a comb for a close 0.5 mm trim.

Corded use only

Power cord provides constant power

Easy to clean

Simply pop the trimmer head open and use the cleaning brush included to sweep away loose hairs.

Follows every curve

The hair clipper gently follows the contours of your head for a fast, even and comfortable haircut.

High performance trimmer

The trimmer blades have extra-sharp, self-sharpening edges to cut hairs neatly and effectively, but with rounded tips to protect your skin.

Skin friendly trimmer

Rounded blade tips prevent skin irritation, while the ultra-sharp cutting edges deliver excellent trimming performance.

Built to last

All of our grooming products are built to last. They come with a 2-year worldwide guarantee and worldwide voltage compatibility.

Specifications

Service

2-year worldwide guarantee

Accessories

Cleaning brush

Cutting system

Comb type: Contour following

Cutter width: 41 mm

Cutting element: Stainless steel blades

Number of length settings: 8

Precision (size of steps): by 2 mm

Range of length settings: from 3 to 15 mm

Self-sharpening stainless steel blades

Small comb (3 to 15 mm)

Design

Shape: Ergonomic

Ease of use

Zoomring

Adjustable guide combs

Power system

Usage: Corded only

