

PHILIPS

10-in-1 Head to toe trimmer

Multigroom series
7000

5 attachments & 5 combs

cordless, showerproof

high-performance blade

50mins cordless use/1h charge

QG3380/16



All-in-one beard, hair & body trimmer

10 in 1 complete trimmer for maximum versatility

Groom your beard, hair and body with this showerproof all-in-one trimmer. 10 different attachments give you the freedom to create different styles from head to toe, while turbo power helps you trim through thick hair evenly and gently.

Versatile

- Trim your face, neck and sideburns to complete your look
- 18 adjustable lengths (1-18 mm) for an even beard or stubble
- 12 adjustable lengths (1-12mm) for an even stubble
- Define sharp lines around your beard or goatee
- Shave small areas on your cheeks and chin with precision
- Tidy up your eyebrows and sideburns to an even length
- Gently get rid of unwanted nose and ear hair
- 18 adjustable lengths (3-20 mm) for an even haircut
- Shave your body with comfort while you are in the shower
- 10 adjustable lengths (3-12mm) for a comfortable body groom

Easy to use

- Skin-friendly, high-performance blades for a gentle trim
- 50 minutes of cordless use on a 1-hour charge
- Higher cutting speed to power through thick hair



asimpleswitch.com


Highlights

Full size metal trimmer




Use the full size metal trimmer without a comb to complete your style and get clean, sharp lines around the edges of your beard.

Beard & stubble comb



Trim your beard to exactly the length you want, by locking in the setting that suits your desired look. The beard & stubble comb offers 18 length settings from 1mm to 18mm, with precisely 1mm between each setting.

Dedicated stubble comb



Trim your stubble to exactly the length you want, by locking in the setting that suits your desired look. The dedicated stubble comb offers 12 length settings from 1mm to 12mm, with precisely 1mm between each setting.

Detail trimmer




Create fine lines, contours and details to define or change your style.

Detail foil shaver




Get rid of unwanted hairs with precision on small areas of your cheeks and chin, for a clean finish.

Detail comb



Precisely comb and trim your eyebrows and sideburns for a finished look.

Nose trimmer




Remove unwanted nose and ear hair, easily and comfortably.

Hair comb



Keep your haircut in style, or create a new one, by trimming to different lengths. The hair comb offers 18 length settings from 3mm to 20mm, with precisely 1mm between each setting.

Bodygroomer



Shave any area below the neck with comfort. The bodygroomer's head is made from a hypo-allergenic foil and has rounded tips to protect your skin.



[asimpleswitch.com](https://www.asimpleswitch.com)

Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

Specifications

Create the look you want

Number of attachments/combs: 5 attachments & 5 combs

Styling tools: Full size metal trimmer, Detail trimmer, Precision shaver, Rotary nose trimmer, Bodyshaver, 18-setting beard&stubble comb, 12-setting stubble comb, Detail & eyebrow comb, 18-setting hairclipper comb, 10-setting body comb

Number of length settings: 18 integrated length settings

Bodygroom/Hairclipping/Facial: Moustache, Long beard, Short beard, Stubble look, Sharp lines, Detailed styling, Goatee

Trimming performance

High-performance blade: For a gentle trim

Turbo power button: For increased performance

Accessories

Pouch: Storage pouch

Oil in pack

Ease of use

Wet & Dry: Showerproof and easy cleaning

Display: Battery full indicator, Charging indicator, Battery low indicator

Design

Color: Black with brushed chrome frame

Handle: Easy grip

Power

Battery type: Ni-MH

Run time: 50 minutes

Charging: 1 hour full charge, 5 min quick charge

Automatic voltage: 100-240 V

Service

2-year guarantee

