

PHILIPS

beard trimmer

Beardtrimmer series
3000

1 mm precision settings

Stainless steel blades

30 min cordless use/8 h charge

USB charging



QT3310/13



Consistent performance time after time Up to 30-min run time with USB cable

This beard trimmer is designed to be charged with any micro-USB cable. It fully charges in 8 hours and runs for up to 30 minutes. The stainless steel blades are self-sharpening, giving you the same hassle-free experience as on day 1.

Skin-friendly performance

- Stainless Steel Blades for long-lasting sharpness
- Skin-friendly blades for zero trim

Precision

- 10 lock-in length settings, 1-mm precision

Easy to use

- 30 minutes' run time after 8 hours' USB charging
- Ergonomic design for easier handling
- Detachable head for easy cleaning
- 2-year guarantee, worldwide voltage, no oiling needed

Highlights

Stainless Steel Blades



Get a perfect yet protective trim, time after time. The trimmer's steel blades lightly brush against one another, sharpening themselves as they trim so they stay extra-sharp and as effective as on day 1.

10 lock-in length settings



10

Get a 3-day shadow look of 1 mm or a full beard of 10 mm in precise 1-mm steps, or remove the comb and get the zero trim look of 0.5 mm.

Cordless use, USB charging



Charge your trimmer for 8 hours with any micro-USB cable to get 30 minutes of cordless use. You can plug it in to your laptop or use an adapter.

Skin-friendly blades



Get a perfect yet protective zero trim, time after time. They also have rounded tips and combs to help prevent skin irritation.

Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

Ergonomic design



Easy to hold and use. Designed to help you trim those hard-to-reach areas.

Built to last



All of our grooming products are built to last. They come with a 2-year worldwide guarantee and worldwide voltage compatibility, and they never need to be oiled.

Specifications

Cutting system

Cutter width: 32 mm

Cutting element: Stainless steel blades

Precision (size of steps): By 1 mm

Range of length settings: 1 up to 10 mm

Non-scratch teeth: For more comfort

Create the look you want

Number of length settings: 10 integrated length settings

Accessories

Maintenance: Cleaning brush

Comb: Stubble comb

Power

Battery Type: NiMH

Run time: 30 minutes

Charging: 8 hours full charge, USB charging

Automatic voltage: 100-240 V

Ease of use

Zoom wheel: Easily adjust length settings

Display: Charging indicator

Cleaning: Washable blades

Operation: Cordless use

Design

Handle: Easy grip

Service

2 year guarantee

No oil needed

