

# PHILIPS

beard and stubble  
trimmer

Beardtrimmer series  
3000

0.5-mm precision settings

Stainless steel blades

45 mins cordless use/10 hr  
charge



QT4005/13



## The perfect beard made easy

The most convenient way to start with your beard

Style your beard the way you want with this beard trimmer. Precision from as short as 0.5mm up to 10mm.

### Precision

- 0.5 mm precision
- Easy to select and lock in length settings, 0.5 mm to 10 mm

### Skin-friendly performance

- Skin friendly rounded tips for smooth skin contact

### Easy to use

- Up to 45 minutes of cordless use after 10 hours' charging
- Ergonomic design for easier handling
- Detachable head for easy cleaning
- 2-year guarantee, worldwide voltage, no oiling needed

# Highlights

## Perfect 3-day beard every day



Set the trimmer at the lowest position for perfect stubble, just 0.5mm long.

## 20 lock-in length settings



Turn the wheel to simply select and lock in the length settings you want: from a 3-day beard of 0.5 mm up to a full beard of 10 mm, in precise 0.5 mm steps.

## Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

## Cordless Use



Rechargeable only. Up to 45 minutes of cordless power after 10 hours of charging.

## Ergonomic design



Easy to hold and use, it's designed to help you trim those hard-to-reach areas.

## Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

## Built to last



All of our grooming products are built to last. They come with a 2 year worldwide guarantee, worldwide voltage and never need oiling.

# Specifications

## Power system

Charging time: 10 hours  
Running time: Up to 45 minutes  
Battery type: Ni-MH  
Worldwide voltage: 100-240 V

## Accessories

Cleaning brush

## Cutting system

Cutter width: 32 mm  
Number of length settings: 20  
Precision (size of steps): by 0.5 mm

Comb type: Stubble

Cutting element: Stainless steel blades

Non-scratch teeth: For more comfort

Range of length settings: 0.5 up to 10 mm

## Design

Handle: Easy grip

## Ease of use

Secured length settings

Zoomring: Easily adjust length settings

Charge indication: On plug

Battery: 1 x AAA NiMH

Easy Cleaning: Washable attachments

## Create the look you want

Styles: Short beard, Stubbled look

## Service

2-year worldwide guarantee

