

PHILIPS

beard trimmer

Beardtrimmer series
3000

0.5mm precision settings

Advanced titanium blades

1h charge/90mins cordless use



QT4011/15



Pro Skin Advanced Trimmer

The most convenient way to start with your stubble

Style your beard the way you want with this stubble and beard trimmer. Precision from as short as 0.5mm up to 10mm.

Precision

- Easy to select and lock-in length settings, 0.5mm to 10mm
- 0.5mm precision

Skin friendly performance

- Superior cutting performance with titanium-coated blades
- Skin-friendly rounded tips for smooth skin contact

Easy to use

- 90 minutes of cordless use after a 1 hour charge
- Ergonomic design for easier handling
- Detachable head for easy cleaning
- 2 year guarantee, worldwide voltage, no oil needed
- Travel and storage pouch

Highlights

20 lock-in length settings



Turn the wheel to simply select and lock-in the length settings you want: from a 3-day beard of 0.5mm up to a full beard of 10mm, in precise 0.5mm steps.

Titanium blades



Advanced titanium blades for superior cutting performance and long-lasting sharpness

Perfect 3-day beard every day



Set the trimmer at the lowest position for a perfect stubble, just 0.5mm long.

Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

Ergonomic design



Easy to hold and use. Designed to help you trim those hard-to-reach areas.

Corded and cordless use



Use it cordless or plugged in. You'll have 90 minutes of cordless power after 1 hour of charging.

Travel and storage pouch



The travel pouch protects your product during traveling and storage.

Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

Built to last



We back this Philips trimmer with a 2-year guarantee: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

Specifications

Cutting system

Cutter width: 32 mm

Number of length settings: 20

Precision (size of steps): By 0.5mm mm

Comb type: Stubble

Cutting element: Stainless steel blades,
Titanium Coated Blades

Non-scratching teeth: For more comfort

Range of length settings: 0.5 up to 10 mm

Create the look you want

Styles: Short beard, Stubble look

Accessories

Cleaning brush

Power system

Battery type: Ni-MH

Running time: 90 minutes

Charging time: 1 hour

Battery Light

Worldwide voltage: 100-240 V

Ease of use

Secured length settings

Zoom wheel: Easily adjust length settings

Battery: 2x AAA NiMH

Charge indication: On plug

Easy Cleaning: Washable attachments

Design

Handle: Easy grip

Service

2-year worldwide guarantee

