

# PHILIPS

Beard trimmer

Beardtrimmer series  
3000

0.5mm precision settings

Advanced titanium blades

120 min cordless use/1h charge



QT4018/15



## Perfect 3 day beard made easy

The most convenient way to start with your stubble

Style your beard the way you want with this stubble and beard trimmer. Precision from as short as 0.5mm up to 10mm.

### Precision

- Easy to select and lock-in length settings, 0.5mm to 10mm
- 0.5mm precision

### Skin friendly performance

- Superior cutting performance with titanium-coated blades
- Skin-friendly rounded tips for smooth skin contact

### Easy to use

- Up to 120 minutes of cordless use after a 1-hour charge
- Ergonomic design for easier handling
- Detachable head for easy cleaning
- Travel and storage pouch
- 2 year guarantee, worldwide voltage, no oil needed

# Highlights

## 20 lock-in length settings



Turn the wheel to simply select and lock-in the length settings you want: from a 3-day beard of 0.5mm up to a full beard of 10mm, in precise 0.5mm steps.

## Titanium blades



Advanced titanium blades for superior cutting performance and long-lasting sharpness

## Perfect 3-day beard every day



Set the trimmer at the lowest position for a perfect stubble, just 0.5mm long.

## Skin-friendly high-performance



Blades stay extra-sharp to always cut hairs neatly and effectively, but have rounded blade tips and combs to prevent irritation.

## Corded and cordless use



Use it cordless or plugged in. You'll have up to 120 minutes of cordless power after 1 hour of charging.

## Easy to clean



Detach the head and rinse it under the tap for easy cleaning. Dry it before you put it back on the appliance.

## Ergonomic design

Easy to hold and use. Designed to help you trim those hard-to-reach areas.

## Travel and storage pouch



The travel pouch protects your product during traveling and storage.

## Built to last



We back this Philips trimmer with a 2-year guarantee: our grooming products are built to last. You'll never need to oil it, and it's compatible with all worldwide voltages.

# Specifications

## Cutting system

**Precision (size of steps):** by 0.5 mm

**Cutter width:** 32 mm

**Cutting element:** Stainless steel blades,  
Titanium Coated Blades

**Number of length settings:** 20

**Comb type:** Stubble

**Non-scratching teeth:** For more comfort

**Range of length settings:** 0.5 up to 10 mm mm

## Create the look you want

**Styles:** Short beard, Stubble look

## Power

**Battery Type:** Lithium-ion

**Run time:** 120 minutes

**Charging:** 1 hour full charge

**Automatic voltage:** 100-240 V

## Accessories

**Travel pouch**

**Cleaning brush**

## Design

**Handle:** Easy grip

## Ease of use

**Display:** Charging indicator, Battery light

**Secured length settings**

**Zoom wheel:** Easily adjust length settings

**Charge indication:** On plug

**Easy Cleaning:** Washable attachments

## Service

**2-year guarantee**

**No oil needed**

