

PHILIPS

NORELCO

Stubble trimmer

0.5-mm precision settings

Diamond-like carbon blades

60 mins' cordless use/1 hr charge



QT4022/41



Perfect stubble

No skin compromise

This Philips stubble beard trimmer delivers superior trimming performance without compromising skin comfort for a perfect stubble beard.

Skin friendly

- Skin friendly rounded tips and combs for smooth skin contact

Easy to use

- 60 minutes of cordless use after a 1-hour charge
- Battery light indicates the battery status (low/ full)
- Ergonomic design for easy handling
- 2-year guarantee, worldwide voltage, no oiling needed
- 100% washable for easy cleaning

Performance

- High-performance self-sharpening blades
- Diamond-like carbon blade stays sharp for longer

Precision

- 0.5-mm stubble settings for a 3-day beard every day
- Easy to select and lock in 20 length settings, from 0.5–10 mm

Highlights

20 locking length settings



Simply select and lock in the length setting you want: from a stubble of 0.5 mm up to a full beard of 10 mm, in precise 0.5 mm steps.

3-day beard, every day

Set the trimmer at the lowest position for a perfect 3-day beard, just 0.5 mm long

Battery light

Battery light glows green when the battery is full, and blinks orange when 10 minutes remain.

Built to last

All of our grooming products are built to last. They come with a 2-year worldwide guarantee and worldwide voltage, and never need oiling

Corded and cordless use



Use it plugged in or cordless. 1 hour of charging gives you 60 minutes of cordless power.

Diamond-like carbon blade



Ensures the cutting element stays sharp 3 times longer than traditional stainless steel blades

Ergonomic design




Comfortable to hold and easy to manoeuvre for hard-to-reach areas.

High-performance trimmer

The trimmer blades have self-sharpening edges that cut hairs neatly and effectively. Blades are extra-sharp but have rounded tips to protect your skin

Skin friendly trimmer



Rounded tips provide smooth skin contact, while the sharp cutting edges deliver a high trimming performance

Easy to clean



To clean the trimmer head, simply rinse it under the tap.

Specifications

Power system

Running time: up to 60 minutes
Charging time: 1 hour
Battery type: Ni-MH

Accessories

Cleaning brush

Cutting system

Comb type: Stubble
Cutter width: 32 mm
Non-scratch teeth: For more comfort

Precision (size of steps): by 0.5 mm

Range of length settings: 0.5 up to 10 mm

Cutting element: Diamond-like carbon blade

Number of length settings: 20

Design

Finishing: Red panels

Soft touch handle

Ease of use

Secured length settings

Wet and Dry: 100 % waterproof for easy use and cleaning

Zoomring: Easily adjust length settings

Create the look you want

Styles: Short beard, Stubble look

Service

2-year worldwide guarantee

