

# PHILIPS

## NORELCO

Series 7000 vacuum  
beard trimmer

Beardtrimmer 7100

Integrated vacuum system

18 built-in length settings

60 mins' cordless use/8 hr  
charge

QT4050/41



## Perfect beard, less mess with new Vacuum System

This Philips vacuum beard trimmer delivers superior trimming performance with an integrated vacuum system to capture hairs during use. Less mess guaranteed.

### **Best performance that feels great**

- Contour-following comb for a precise and even trim

### **Provides maximum ease of use**

- Clear view hair chamber for visual control
- Maintenance-free blades
- Vacuum system captures cut hairs for mess-free trimming

### **Create the look you want**

- 18 secured length settings from 1 mm up to 18 mm

### **Provides optimal power**


- Strong lithium-ion battery for optimal power use
- Corded and cordless use for maximum power and freedom



[asimpleswitch.com](http://asimpleswitch.com)


# Highlights

## 18 secured length settings



Select and locks your desired length within a versatile range of possible lengths.

## Clear view hair chamber



Transparent hair chamber makes it easy to see when the chamber needs to be emptied.

## Contour-following comb



The flexible guide comb automatically follows every curve of your face to achieve an even trim easily and comfortably.

## Maintenance-free blades



The blades stay sharp and need no oiling, so your product is always ready for use.

## Integrated vacuum system




The integrated vacuum mechanism absorbs cut-off hairs during use and gives you a cleaner washbasin after use.

## Powerful Lithium-Ion battery



This product has a powerful lithium-ion battery with quick charge so you can charge the product in 8 hours for 50 minutes use.

## Corded and cordless use



Use your trimmer corded or cordless with the recharged battery for maximum power and freedom.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Cutting system

Cutter width: 32 mm

Number of length settings: 18

Range of length settings: 1 to 18 mm

Precision (size of steps): by 1 mm

Self-sharpening stainless steel blades

Cutting element: Stainless steel blades

Comb type: Contour following

Non-scratch teeth: For more comfort

## Ease of use

Vacuum system: For hair collection

Zoomring: Easily adjust length settings

Secured length settings

Charging indicator: 2 LEDs

Maintenance-free: No oil needed

## Power system

Battery type: Li-Ion

Running time: 50 minutes

Usage: Corded/cordless

Charging time: 8 hours

## Design

Finishing: Black side panels

Soft touch handle

## Accessories

Cleaning brush

## Service

2-year worldwide guarantee

## Create the look you want

Styles: Short beard, Full beard

