

PHILIPS

Vacuum stubble
and beard trimmer

50 min grooming

Precision: 1-18 mm

QT4070/32



Perfect even stubble

The only stubble trimmer with a vacuum system

This powerful stubble and beard trimmer delivers superior trimming performance. The stubble comb has been specially designed to create the perfect stubble you want. The integrated vacuum system captures hairs for no mess guaranteed.

Best performance that feels great

- Contour following comb for a precise and even trim

Provides optimal power

- Coded and cordless use for maximum power and freedom
- Strong lithium-ion battery for optimal power use
- Turbo power boost button boosts cutting and fan speed

Create the look you want

- 18 secured length settings from 1mm up to 18mm
- Stubble comb designed to trim with more precision

Brings maximum ease of use

- Maintenance free blades
- Multifunctional display
- Travel Lock
- Vacuum system captures cut hairs for mess-free trimming

Highlights

18 secured length settings

Select and locks your desired length within a versatile range of possible lengths.

Contour following comb

Flexing guide comb that follows automatically every curve of your face for getting an even trim in a easy and comfortable way.

Corded and cordless use

Use your Philips trimmer corded or cordless with the recharged battery for maximum power and freedom.

Maintenance free blades

The blades stay sharp and need no oiling, so your product is always ready for use.

Multifunctional display

Multi-functional display showing battery status and hair length

Powerful Lithium-Ion battery

This product has a powerful lithium-ion battery with quick charge so you can charge the product in only 1 hour for 50 minutes use.

Stubble comb

The stubble comb has been designed for giving more sight while you are trimming as there are no frontal teeth. Moreover, by applying the tip of the trimmer fine contours are possible, by applying the trimmer at different angle on the skin you get more control on individual hair length. This comb is ideal for a perfect stubble or a 5 o'clock shadow where every detail counts.

Travel lock

Travel lock option protects your product against unintentionally switching on when you are wearing it in your bag.

Turbo power boost button

When greater suction power and increased cutting speed is desired while trimming, simply press the Turbo Power Button.

Integrated vacuum system

The integrated vacuum mechanism absorbs cut-off hairs during use and gives you a cleaner washbasin after use.

Specifications

Cutting system

Cutter width: 32 mm
Number of length settings: 18
Range of length settings: 0.5 up to 18 mm
Precision (size of steps): by 1 mm
Self-sharpening stainless steel blades
Cutting element: Stainless steel blades
Comb type: Contour following, Stubble
Non-scratching teeth: For more comfort

Ease of use

Vacuum system: For hair collection
Zoomring: Easily adjust length settings
Secured length settings
Multifunctional display: Battery indication, Charging indication, Length setting indication
Maintenance free - No Oil need

Power system

Battery type: Li-ion
Quick charge: 1 hour(s)
Running time: 50 minutes

Design

Finishing: White side panels
Soft touch handle

Accessories

Cleaning brush

Service

2-year worldwide guarantee

Create the look you want

Styles: Short beard, Stubble look

Performance

Trimming performance: Turbo power boost button

