

PHILIPS

Vacuum stubble and beard trimmer

Pro

With multifunctional display

QT4075



Perfectly even stubble

The only stubble trimmer with a vacuum system

This powerful stubble and beard trimmer delivers superior trimming performance. The stubble comb has been especially designed to create the perfect stubble you want. The integrated vacuum system captures hairs for no mess guaranteed.

Provides maximum ease of use

- Clear view hair chamber for visual control
- Maintenance-free blades
- Multifunctional display
- Travel Lock
- Vacuum system captures cut hairs for mess-free trimming

Create the look you want


- 18 secured length settings from 1 mm up to 18 mm
- Stubble comb designed to trim with more precision
- Stubble setting for a 5 o'clock shadow look

Provides optimal power

- Corded and cordless use for maximum power and freedom
- Strong lithium-ion battery for optimal power use
- Turbo power boost button boosts cutting and fan speed

Highlights

18 secured length settings



Select and locks your desired length within a versatile range of possible lengths.

Multifunctional display



Multifunctional display shows the length setting easily

Travel lock



Travel lock option protects your product against unintentionally switching on when you are carrying it in your bag.

Clear view hair chamber



Transparent hair chamber makes it easy to see when the chamber needs to be emptied.

Powerful Lithium-Ion battery




This product has a powerful lithium-ion battery with quick charge so you can charge the product in only 1 hour and get 50 minutes of use.

Turbo power boost button



When greater suction power and increased cutting speed is desired while trimming, simply press the Turbo Power Button.

Corded and cordless use



Use your Philips trimmer corded or cordless with the recharged battery for maximum power and freedom.

Stubble comb

The stubble comb has been designed to increase visibility during trimming as there are no frontal teeth. Moreover, fine contours are possible by applying the tip of the trimmer at different angles on the skin. This allows for greater control with each individual hair length. This comb is ideal for a perfect stubble or a 5 o'clock shadow where every detail counts.

Integrated vacuum system




The integrated vacuum mechanism absorbs cut-off hairs during use and gives you a cleaner washbasin after use.

Maintenance-free blades



The blades stay sharp and need no oiling, so your product is always ready for use.

Stubble setting



If you want short stubble of 0.5 mm for a perfect 5 o'clock shadow look, use the Philips trimmer without the trimming comb.

Specifications

Cutting system

Cutter width: 32 mm

Number of length settings: 18

Range of length settings: 0.5 up to 18 mm

Precision (size of steps): by 1 mm

Self-sharpening stainless steel blades

Cutting element: Stainless steel blades

Comb type: Stubble

Maintenance free - No Oil needed

Non-scratch teeth: For more comfort

Ease of use

Vacuum system: For hair collection

Zoomring: Easily adjust length settings

Secured length settings

Multifunctional display: Battery indication,
Charging indication, Length setting indication

Power system

Battery type: Li-Ion

Quick charge: 1 hour(s)

Running time: 50 minutes

Design

Finishing: Chromed side panels

Soft touch handle

Accessories

Cleaning brush

Service

2-year worldwide guarantee

