

PHILIPS

EcoPro61 Slim

EcoPro

270° Multi-angle and Foldable

3 light modes: 500, 250, 50 lm

140 lm spotlight

Long-life battery up to 20 hrs



RC620X1



Quality light to get the job done

Ultra-slim design to light up narrow spaces

The versatile, ultra-slim and rechargeable Philips EcoPro61 Slim is ideal for lighting up narrow spaces with its 270° rotating lighting module. Its long-lasting battery life of up to 20 hours allows you to work a full day without interruption.

Ultra-slim design to light up narrow spaces

- Ultra-slim, 270° pivoting design to light up narrow spaces

3 light modes for different uses

- 3 light output levels for the flexibility you need

140 lm spotlight

- 140 lm pointer for spot inspection

Long-life battery up to 20 hours

- Long-life battery up to 20 hours

Hands-free working

- 360° hook and strong magnet

Specifications

Ordering information

Order entry: RC620X1
Ordering code: 484031

Electrical characteristics

Battery capacity: 2500 mAh
Voltage: 3.7 V
Battery run time (eco): 20 h at 50 lm; 5 h at 250 lm
Battery type: Li-ion battery
Charging cable type: Micro USB cable
Plug type: Micro USB
Battery charging time: up to 3.2 hours
Power Source: Rechargeable battery
Wattage: 5 W + 3 W Torch
Battery run time (boost): Up to 2.2 hours

Light characteristics

Light output (pointer): 140 lumens
Light intensity (boost): 792 lux at 0.5 m
Light intensity (eco): 396 lux/80 lux at 0.5 m
LED lifetime: >10,000 hours
Beam angle: 90°
Light output (eco): 250/50 lumens
Colour temperature: Cool colour
Beam angle (pointer): 30
Light intensity (Pointer): 450 lux at 0.5 m
Light output (boost): 500 lumens

Outer pack information

Gross weight per piece: 350 g
Height: 21.3 cm
Length: 10.2 cm
Width: 5.3 cm

Packaging Data

EAN1: 8719018004840
EAN3: 8719018004857

Packed product information

Height: 16.5 cm
Length: 3.1 cm
Pack Quantity / MOQ: 1
Weight with batteries: 230 g g
Width: 5.1 cm
Size: Slim
Cable length: 1 m Micro USB cable

Product description

Hook: Stainless foldable hook
Impact protection rating (IK): IK07
Ingress protection rating (IP): IP20
Magnet: Strong magnet
Materials and finishing: PC+TPE
Resistant to: grease, oil, workshop solvents
Technology: LED Lamp
UV leak detector: No
Hands-free options: Hook
Operating Temperature: 0°C to 40°C
Number of LEDs: COB+1 LED (torch)
Pointing light
Lamp type: Rechargeable
Range: EcoPro

Marketing specifications

Product highlight: Multi-Angle Slim LED work lamp
Expected benefits: See better, Work better

Highlights

Ultra-slim, rotatable design

The Philips EcoPro61 has been designed with a 270° lighting module so you can easily direct the light beam and illuminate extremely narrow spaces. Its ultra-slim design (1.6-m wide head) eliminates blind spots deep inside your engine or machinery.

3 light modes

Different jobs demand different amounts of light. With its three power modes, the Philips EcoPro61 Slim lets you adjust the light to your needs. Boost mode gives you a powerful 500-lumen light output, helping you to spot even the smallest of details. If the ambient light changes or if you just want to preserve the battery, switch to Eco mode from 50 to 250 lumen and use your lamp for up to 20 hours. What's more, the EcoPro61 Slim's 6500-Kelvin temperature is gentle on your eyes, preventing fatigue.

140 lm spotlight

Philips EcoPro61 Slim offers you a spotlight combined with a lamp delivering 140 lumen. You'll be able to see small details even in dark corners. The spotlight can be used in both positions: with the lamp folded and with the lighting module open.

Long-life battery

Once fully charged, your Philips EcoPro61 Slim delivers 2.5 hours of continuous bright light from its main 500-lumen beam. The 50-lumen Eco mode lasts up to 20 hours. So with occasional use, the lamp can last days before requiring a recharge.

Hands-free working

The 360° retractable, stainless-steel hook lets you hang this lamp anywhere you need. It also attaches easily to any metal surface, leaving both your hands free to work.

