



Gaggia
Fully automatic
espresso machine

RI8176/50

A SINGLE TOUCH TO TASTE A GREAT ITALIAN ESPRESSO

ENJOY YOUR FULLY CUSTOMISED ESPRESSO

soft touch ring menu

Easy to clean and maintain

- Automatic cleaning and de-scaling
- Removable brewing group

Easy to use

- Cup warmer
- One-touch personalised interface
- Pannarello to froth milk as you like
- Touch lift

Bean- to-cup customisation

- Patented adjustable espresso crema and body structure

GAGGIA
MILANO

HIGHLIGHTS

SPECIFICATIONS

Cup warmer



This feature allows you to not only store your cups and glasses directly on the machine, it also pre-heats them, releasing the aroma even more and guaranteeing a long-lasting crema

Auto cleaning and de-scaling



Easy to use and easy maintenance: Thanks to the automatic cleaning and de-scaling cycles, you are guaranteed perfect enjoyment every day and maximum longevity for your automatic espresso machine.

One-touch interface

The wide and easy-to-read display allows one-touch functionality and intuitive handling.

Pannarello



With the pannarello you can froth your milk exactly how you like it. Just dip the pannarello in the milk and

stir slowly in a circular motion. Froth the milk for as long as you want to create more or less foamy milk.

Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert — finished.

SBS (Saeco brewing system)



The Philips Saeco automatic espresso machine exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. Simply by turning the knob you can prepare the crema exactly according to your taste. A little knob that makes a big difference.

Touch lift



Patented electronically adjustable drip tray to fit every cup size