



Saeco Incanto
Super-automatic
espresso machine

- de luxe
- Silver

RI9724/47

The great Incanto line: in a class of its own

Experience the dream of every coffee lover.

Saeco Incanto line

Grind your favorite coffee beans

- Play with the coffee's richness with our adjustable grinders
- Bean to cup system
- Adjust coffee length, temperature and strength
- Patented adjustable espresso crema and body structure

Easy to use

- Delicious milk froth thanks to the classic milk frother
- Cup warmer
- Ergonomic in day-by-day operations

Ease of cleaning and maintaining

- Always a clean machine thanks to auto-clean and descaling
- Easy cleaning thanks to removable brewing group

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Coffee customization



With Saeco full automatic machines, you can customize your espresso as you like it: from a strong short espresso to a mild long coffee

SBS (Saeco Brewing System)



Saeco automatic espresso machine exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. Simply by turning the knob you can

prepare the crema exactly according to your taste. A little knob that makes a big difference.

Bean to cup system



It means that whole coffee beans are freshly ground and directly processed for each and every beverage.

Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is

immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Ergonomy



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments are directly accessible.

Auto cleaning and descaling



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee. Regular descaling prolongs your espresso machine's life. This machine will not only prompt when descaling is needed, the automated descaling process will start on your machine and guides you with clear on-screen messages when you have to intervene. Descaling has never been so easy!

Specifications

Technical specifications

- Boiler material: Stainless steel (Inox)
- Power: 1250 W
- Voltage: 120 V
- Frequency: 60 Hz
- Cord length: 80 cm

Perfect Espresso

- Espresso technology: Aroma-system: pre-brewing,

SBS: creme adaptor, Cup warmer

Weight and dimensions

- Product dimensions (L x D x H): 305 x 394 x 381 mm
- Product weight: 11 kg
- Coffee bean capacity: 300 gr
- Waste container capacity: 12 servings
- Water tank capacity: 2 L