



Saeco Odea
Super-automatic
espresso machine

- Classic Milk Frother
- Silver

RI9752/48

Espresso in a trendy and functional design

Odea standard line

Odea standard line

Authentic Italian coffee perfection

- Delicious milk froth thanks to the classic milk frother
- Coffee without waiting thanks to the quick heat boiler
- Every bean ground perfectly with our metal grinders

Set the beverages to suit your taste

- Save your favorite coffee length
- Play with the coffee's richness with our adjustable grinders

Ease of cleaning and maintaining

- Always a clean machine thanks to automatic circuit cleaning
- Easy cleaning thanks to removable brewing group

PHILIPS

Saeco, a Philips brand

 **Saeco**



Highlights

Automatic circuit cleaning



Saeco designed this espresso machine to automatically clean its coffee circuit with water upon starting up or switching off of the machine, this delivers a great, fresh taste with each cup of coffee.

Quick heat boiler



The Saeco quick heat boiler technology ensures your machine is always ready. Now you won't have to wait between brewing each espresso, but can prepare coffee after coffee.

Saves your coffee length



You will always get a perfect cup of espresso brewed according to your personal preference

thanks to our memo function which allows you to adjust the coffee length to suit your taste. Enjoy a superb coffee drink with just the press of a button.

Classic milk frother



This Saeco espresso machine comes with the classic milk frother that baristas call a "Pannarello". It dispenses steam and is immersed in milk to prepare gorgeous milk foam. Unleash your inner barista by preparing your delicious milk specialties the traditional way!

Metal grinders



Our metal grinders always guarantee impeccable grinding.

5 step adjustable grinders



Different coffee blends require different levels of granularity for the full flavor to unfold. The grind granularity of this espresso machine can be adjusted in 5 settings, from the finest grind, for a full bodied espresso, to the coarsest, for a lighter coffee.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

Specifications

Service

- 1-year guarantee

Perfect Espresso

- Espresso technology: Saeco adapting system,
Aroma-system: pre-brewing

Technical specifications

- Supported coffee types: Whole coffee beans
- Water pressure in pump: 15 bar (perfect espresso)
- Removable brewing group
- Country of origin: Designed in Italy, Made in Europe
- Cord length: 80 cm
- Number of water boilers: 1 boiler
- Frequency: 60 Hz

- Power: 1400 W
- Voltage: 120 V
- Boiler material: Stainless steel (Inox)

Weight and dimensions

- Product weight: 8.5 kg
- Product dimensions (L x D x H): 292 x 381 x 368 mm
- Coffee bean capacity: 180 gr
- Waste container capacity: 14 servings
- Water tank capacity: 1.5 L
- Maximum cup height: 150 mm

Design

- Colour: Stainless steel
- Materials and finishing: Plastic