



Saeco Talea  
Automatic espresso  
machine

- Touch
- Plus

RI9828/01

# Elegant cafè-style enjoyment awaits you

## Enjoy your fully customised espresso

Talea standard line

### **Bean- to-cup customisation**

- Adjust coffee length, intensity, temperature and strength
- Patented adjustable espresso crema and body structure

### **Easy to use**

- Pannarello to froth milk as you like
- Touch lift
- Cup warmer
- Touch screen
- Ergonomic in day to day operation

### **Easy to clean and maintain**

- Automatic cleaning and de-scaling
- Removable brewing group

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## Coffee Customisation



With Saeco you can always easily select the coffee length, intensity, temperature and strength you prefer. Your personal settings are memorised, so you can enjoy your favourite coffee at the touch of a button.

## SBS (Saeco Brewing System)



The Philips Saeco automatic espresso machine exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. Simply by turning the knob you can prepare the crema exactly according to your taste. A little knob that makes a big difference.

## Cup warmer



This feature allows you to not only store your espresso cups and glasses right on the espresso

machine, it also pre-heats them letting the aroma unfold even better and guaranteeing a long-lasting crema

## Touch lift



Patented electronically adjustable drip tray to fit every cup size

## Touch screen

Touch screen user interface — amber colour

## Pannarello



With the pannarello you can froth your milk exactly how you like it. Just dip the pannarello in the milk and stir slowly in a circular motion. Froth the milk for as long as you want to create more or less foamy milk.

## Ergonomy



Saeco is a synonym for convenience: refilling beans or water, emptying the coffee-dump box or the drip tray, all compartments are directly accessible.

## Auto cleaning and de-scaling



Easy to use and easy maintenance: Thanks to the automatic cleaning and descaling cycles, you are guaranteed perfect enjoyment every day and maximum longevity for your automatic espresso machine.

## Removable brewing group



The brewing group is at the heart of every fully automatic coffee machine and it should always be kept clean. A task that doesn't get any more convenient than with a Saeco: remove, rinse and re-insert — finished.

# Specifications

## Perfect Espresso

- Espresso technology: Saeco adapting system,  
Aroma-system: pre-brewing, SBS: creme adaptor,  
Cup warmer

- Power: 1400 W
- Voltage: 230 V
- Pump Pressure: 15 Bar

## Technical data

- Boiler: Stainless steel
- Frequency: 50 Hz

## Weight and dimensions

- Coffee bean capacity: 250 gr
- Dump box capacity: 14 servings
- Water tank capacity: 1.7 l