



Saeco

RI9833/61

# Cafe enjoyment in perfect style

Compact and high performing

With the Saeco Syntia, the enjoyment starts as soon as you unwrap it from its packaging.

#### Perfect espresso

- Ceramic grinders for Aroma preserving
- Pre-brewing function for flavour enhancing

#### Easy to use

- Frontal access for easy filling and emptying
- One-click removable brewing group

#### Easy to clean and maintain

- Automatic coffee circuit cleaning
- Descaler Warning

#### Family friendly

- Energy efficient
- Sound-damping system

**PHILIPS**

Saeco, a Philips brand

 **Saeco**



# Highlights

## Pre-brewing system

Pre-brewing for even more enjoyment. Thanks to the Pre-brewing Technology, the coffee grounds are moistened before the actual brewing process – ensuring that the aroma unfolds even better.

## Ceramic grinders

These high-tech grinders beat the competition's steel grinders on many levels: always the perfect Italian taste because of consistent accurate grinding without overheating, supreme longevity and super-silent operation.

## Easy frontal access

All the components you need to reach during your day-to-day enjoyment (water, coffee beans and coffee grounds container, drip tray, removable brewing group) are completely independent and accessible from either the front or top of the machine.

## Energy efficient

This feature keeps the power consumption to a minimum. In fact, less than 1 Watt per hour is needed in stand-by mode, which is switched to automatically after 1 hour, saving resources and money

## Sound-damping system

Special insulation and super-silent ceramic grinders preserve the peaceful kitchen atmosphere

## Auto coffee circuit cleaning



This feature makes sure that each and every coffee is as fresh as possible: Before going into and when

returning from stand-by mode, the machine automatically cleans its coffee circuit.

## Descaler Warning



Dedicated led to advise the end user that the machine needs to be descaled

## One-click removable group



The brewing group – a Saeco invention - is the heart of our machines, ensuring that the machine makes everything on its own. Thanks to its easy access, you can effortlessly remove it for regular cleaning with just one click.

# Specifications

## Perfect Espresso

- Espresso technology: Saeco adapting system, Aroma-system: pre-brewing

## Multi-Beverage

- Milk Variations: Pannarello: milk frothing

## Easy to use

- Cleaning and maintenance: Automatic coffee circuit rinse
- Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Rapid steam, Removable brewing group, Removable water tank

## Technical data

- Boiler: Stainless steel
- Frequency: 50 Hz
- Power: 1400 W
- Voltage: 230 V
- Pump Pressure: 15 Bar

## Weight and dimensions

- Coffee bean capacity: 250 gr
- Dump box capacity: 8 servings
- Water tank capacity: 1.2 l