



Saeco Xelsis
Super-automatic
espresso machine

• Digital ID

RI9946/01

Always following your premium taste

The ultimate Saeco espresso machine

Espresso has always been more than a beverage. Its aroma, its intensity, its countless delicious variations, its joining spirit - a good espresso. The Saeco Xelsis brings this Espresso Feeling to your very own kitchen.

Perfect espresso

- Ceramic grinders for Aroma preserving
- Multi-dimensional adjustable coffee dispensor

Personalize your beverage

- Multi user, multi beverage (6x6)
- Milk and foam level selector
- Integrated automatic milk function
- Patented adjustable espresso crema and body structure

Easy to use

- One touch personalized interface
- Easy cleaning thanks to removable brewing group

PHILIPS

Saeco, a Philips brand

 **Saeco**




Highlights

Multi user, multi beverage

6 one-touch beverages that can be personalised by 6 user profiles – every family member gets his or her favourite customized specialty with just one touch of a button.

Automatic milk function



With the integrated milk frother, all you have to do is filling it with milk and simply pressing the cappuccino button. Your drink will be served within seconds as creamy froth milk will be poured automatically into your beverage.

One touch interface

The wide and easy-to-read display allows onetouch-functionality and intuitive handling.

Milk and foam level selector

For an even wider selection of drinks the automatic and integrated milk frothing function with removable carafe can be set at different levels. It is therefore easy to get hot milk for a cafe latter or perfect foam for a cappuccino.

Ceramic grinders

The high-tech grinders of this coffee machine beat the competition's steel grinders on many levels: always perfectly Italian taste because of consistently accurate grinding without overheating, supreme longevity, super-silent operation.

Adjustable coffee dispenser

No matter what your favourite glass or cup is – with one movement the multi-dimensional coffee

dispenser is adjusted to its size so the full taste and aroma is always perfectly captured.

Removable brewing group



The brewing group, a Saeco invention, is the heart of our espresso machines, ensuring automation. The brewing group is, depending on the model, easily accessible from the front or side. It can be removed effortlessly for easily cleaning by rinsing under the tap ensuring maximum hygiene.

SBS (Saeco Brewing System)



Saeco automatic espresso machine exclusively allows you to adjust your espresso's intensity, altering the crema and body structure as it is dispensed. Simply by turning the knob you can prepare the crema exactly according to your taste. A little knob that makes a big difference.

Specifications

Perfect Espresso

- Espresso technology: Saeco adapting system, Aroma-system: pre-brewing, SBS: creme adaptor

Multi-Beverage

- Milk Variations: Frothing degree adaptor, Integrated auto milk function, Milk quantity selector, Removable milk carafe

Easy to use

- Cleaning and maintenance: Automatic coffee circuit rinse, Automatic milk circuit rinse, Descaling cycle
- Usage: Adjustable coffee dispenser, Bypass for grinded coffee, Cup holding surface, Frontal access to all function, Instant steam (2 boilers), Removable brewing group, Removable watertank

Energy saving

- Energy saving: Selectable Eco-mode

Technical data

- Boiler: Stainless steel
- Frequency: 50 Hz
- Power: 1500 W
- Voltage: 230 V
- Pump Pressure: 15 bar

Weight and dimensions

- Coffee bean capacity: 350 gr
- Waste container capacity: 14 servings
- Milk carafe capacity: 0.5 L
- Water tank capacity: 1,6 L