

PHILIPS

Wet and dry electric shaver

Shaver series 3000

ComfortCut Blade System

4-direction Flex Heads

Pop-up trimmer



S3350/06



Great skin protection, smooth shave wet shave with shaving gel or foam

Now enjoy a refreshing shave without worrying about damaging your skin. The Aquatec seal ensures a comfortable dry shave and a refreshing wet shave. Use it wet with shaving gel or foam for enhanced skin comfort.

A comfortable shave

- Get a comfortable dry or refreshing wet shave with Aquatec
- Rounded edges move smoothly over skin for a protective shave

Adjusts to every curve of your face and neck

- Heads flex in 4 directions to easily shave every curve

Easy to use

- Consistent maximum power year after year
- 45 minutes of cordless shaving after an eight-hour charge
- One touch open, for easy cleaning
- Cordless operation only

Get the most out of your shaver

- Perfect for trimming your sideburns and mustache

Highlights

Aquatec Wet & Dry



Choose how you prefer to shave. With the Aquatec Wet & Dry seal, you can opt for a quick yet comfortable dry shave. Or you can shave wet – with gel or foam – even under the shower.

ComfortCut Blade System




Get a comfortable dry shave. Our ComfortCut Blade System with rounded profile heads glide smoothly across your skin while protecting it from nicks and cuts.

4-direction Flex Heads



Flex heads with 4 independent movements adjust to every curve of your face, giving you an easy shave even on the neck and jaw line.

45 minutes of cordless shaving



You'll have 45+ minutes of running time – that's about 15 shaves – on an eight-hour charge. This shaver only operates in cordless mode.

Li-ion power



Shave longer with every charge. Your shaver will keep going just as strong for years, thanks to our powerful and efficient lithium-ion battery.

OneTouch Open



Simply pop the heads open, and rinse thoroughly under the tap.

Pop-up trimmer



Complete your look by using the pop-up trimmer. Perfect for maintaining a mustache and trimming sideburns.

Cordless use



This shaver is designed to operate only in cordless mode. Always unplug it before shaving.

Specifications

Shaving Performance

Shaving system: ComfortCut Blade System

Contour following: 4-direction Flex Heads

Accessories

Pop-up trimmer included

Maintenance: Protective cap

Ease of use

Display: Battery low indicator, Replace shaving heads indicator

Cleaning: Fully washable

Operation: Cordless use, Unplug before use

Design

Handle: Ergonomic grip & handling

Color: Precision black black

Power

Battery Type: Lithium-ion

Run time: 45 min / 15 shaves

Charging: 8 hours full charge

Automatic voltage: 100-240 V

Max power consumption: 9 W

Stand-by power: 0.1 W

Service

2-year guarantee

Replacement head: Replace every 2 yrs with SH30

