

# PHILIPS

## NORELCO

Wet & dry electric  
shaver, Series 5000

Shaver 5700

MultiPrecision Blade System

5-direction Flex Heads

SmartClick precision trimmer

SmartClean System



S5370/84



## Turbo-powered shave

10% more power\*

The Shaver 5700 adds speed to your morning routine with Turbo mode and a fast, MultiPrecision blade system. The SmartClean system keeps your shaver like new, day after day.

### A close and comfortable shave

- Shave through dense parts of beard with 10% more power
- Blades raise then cut long and short hairs for a fast shave
- Lifts hairs to cut comfortably close

### A comfortable shave

- Heads flex in 5 directions for a fast and close shave
- Get a comfortable dry or refreshing wet shave

### Get the most out of your shaver

- Click-on trimmer for perfect mustache and sideburn trimming
- Keep your shaver like new with SmartClean

### Easy to use

- Up to 45 minutes of cordless shaving power
- Fully charges in 1 hour or 5 minute quick charge
- 3-level battery and travel lock Indicators
- Shaver can be rinsed clean under the tap



asimpleswitch.com

# Highlights

## Turbo mode



Shave even faster through dense parts of your beard with the 10% extra power boost you get by activating Turbo mode.

## MultiPrecision Blade System




Shave with fewer passes for more comfortable skin. The MultiPrecision Blade system raises and cuts long hairs, flat-lying hairs and short stubble in just a few strokes.

## 5-direction Flex Heads



Heads independently move in 5 directions to ensure close skin contact for a faster and closer shave, even on neck and jaw line.

## Use Wet & Dry



Shave in the shower. Or use with water, foam, or gel for a refreshing, comfortable shave.

## SmartClick precision trimmer




Click on our skin-friendly precision trimmer to finish your look. It's ideal for maintaining your mustache and trimming your sideburns.

## SmartClean System



At the touch of a button, SmartClean cleans, lubricates and charges your shaver, keeping it performing at its best.

## 45 minutes of cordless shaving




A powerful Lithium-ion battery gives you more shaves per charge. You'll have 45 minutes of shaving time - that's around 15 shaves - after 1 hours of charging. Plug it in for 5 minutes and you'll have enough power for one shave.

## 1-hour charging time



Shave longer with every charge, thanks to our powerful and long-lasting Lithium-ion battery. Do a quick charge for 5 minutes and you'll have enough power for one shave.

## Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Shaving Performance

**Turbo mode:** Shave with 10% extra power

**Contour following:** 5-direction Flex Heads

**Shaving system:** MultiPrecision Blade System, Super Lift & Cut Action

**SkinComfort:** AquaTec Wet & Dry

## Accessories

**SmartClick:** Precision trimmer

**SmartClean:** Cleans, Charges, Lubricates, Cleaning cartridge (included)

**Maintenance:** Protective cap

## Ease of use

**Display:** 3 level battery indicator, Battery low indicator, Charging indicator, Cleaning indicator, Replace shaving heads indicator, Travel lock indicator

**Cleaning:** Fully washable

**Operation:** Unplug before use

## Design

**Handle:** Ergonomic grip & handling

**Color:** Super Nova Silver - Super Nova Silver

## Power

**Automatic voltage:** 100-240 V

**Run time:** 45 min / 15 shaves

**Battery Type:** Lithium-ion

**Charging:** 1 hour full charge, Quick charge 5 min for 1 shave

**Max power consumption:** 9 W

**Stand-by power:** 0.1 W

## Service

**2-year warranty**

**Replacement head:** Replace every yr with SH50

