

# PHILIPS

Wet and dry electric shaver

Shaver series 9000

V-Track Precision Blades

8-direction ContourDetect Heads

Cleansing brush and P. trimmer



S9111/43



## Perfection in every pass

Cuts up to 20% more hair\* in a single pass

The Shaver 9000 is our most advanced shaver yet. The unique contour-detect technology offers exceptional coverage over every contour of your face, and the V-Track system guides hairs into the best cutting position for the closest results.

### Designed for perfection

- Blades perfectly guide hairs into position for a close shave
- Heads flex in 8 different directions for a superb result

### A comfortable shave

- Get a comfortable dry or refreshing wet shave with Aquatec

### Easy to use

- Intuitive icons make the functions easy to use
- 50 minutes' cordless shaving after a one-hour charge
- Shaver can be rinsed clean under the tap
- With 2 year guarantee

### Get the most of your shaver

- Click-on trimmer for perfect moustache and sideburn trimming
- Click-on brush for thorough facial cleansing



asimpleswitch.com

# Highlights

## V-Track precision blade system



Get the perfect close shave. The V-Track Precision Blades gently position each hair in the best cutting position, even flat-lying hairs and hairs of different lengths. Cuts 30% closer in fewer strokes, leaving your skin in great condition.

## 8-direction ContourDetect Heads



Follow every contour of your face and neck with 8-directional ContourDetect heads. You'll catch 20% more hairs with every pass, resulting in an extremely close, smooth shave.

## Aquatec Wet & Dry



Choose how you prefer to shave. With the Aquatec Wet and Dry seal, you can opt for a quick yet comfortable dry shave. Or you can shave wet—with gel or foam—even under the shower.

## SmartClick precision trimmer



Click on our skin-friendly Precision Trimmer to finish your look. It's ideal for maintaining your moustache and trimming your sideburns.

## SmartClick cleansing brush



Click on brush to cleanse more thoroughly than by hand\*. Use it with the cleanser of your choice. It removes dead skin cells and increases micro-circulation, leaving your skin feeling fresh and radiant.

## 3-level LED display



The intuitive display shows relevant information, enabling you to get the best performance out of your shaver: - 3-level battery and travel lock indicators - Cleaning Indicator - Battery Low Indicator - Replacement Head Indicator

## 50 minutes of cordless shaving



Our advanced charging system gives you two convenient options: charge for one hour and you'll get 50 minutes of running time, or do a quick charge for one full shave. All 9000 Series Shavers contain a powerful, energy-efficient, long-lasting lithium-ion battery. They are designed to operate only in cordless mode to ensure you'll always be safe when shaving with water, even in the shower.



## iF DESIGN AWARD 2015

Shaver series 9000Precision, control and manoeuvrability are the defining features of the 9000 shaver. The V-Track system guides hairs into the best cutting position for the closest result, while fully flexible eight-directional heads catch more hairs for a clean shave in fewer strokes. The "AquaTec Wet and Dry" seal of this shaver allows for a comfortable dry shave or a refreshing wet shave, using a shaving gel or foam for extra skin comfort.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas — Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Shaving Performance

**Shaving system:** V-Track Precision Blade System, Super Lift & Cut Action

**Contour-following:** 8-direction ContourDetect Heads

**Skin comfort:** Aquatec Wet and Dry

## Accessories

**SmartClick:** Precision trimmer, Deep facial cleansing brush

**Pouch:** Travel pouch

## Ease of use

**Display:** 3 level battery indicator, Cleaning indicator, Battery low indicator, Replace shaving heads indicator, Travel lock indicator

**Cleaning:** Fully washable

## Design

**Colour:** Glacier Blue

**Handle:** Ergonomic grip and handling

## Power

**Battery Type:** Lithium-ion

**Run time:** 50 min / 17 shaves

**Charging:** Quick charge for 1 shave, 1 hour full

charge

**Automatic voltage:** 100-240 V

**Max power consumption:** 9 W

**Stand-by power:** 0.1 W

## Service

**2 year guarantee**

**Replacement head:** Replace every 2 yrs with SH90

