



Wet & dry electric shaver, Series 9000 with SmartClean System and Shave Wet or Dry

- V-Track Precision Blades
- 8-direction ContourDetectHeads
- SmartClean System

S9311/84

Perfection in every pass

Cuts up to 20% more hair* in a single pass

The Philips Norelco Shaver 9300, our most advanced wet & dry electric shaver, cuts hairs up to 30% closer to the skin using V-Track precision blades.* Its shaving heads move in 8 directions to cut up to 20% more hair in a single pass.*

Benefits

Designed for perfection

- Heads move in 8 directions for an extremely close result
- Uniquely designed shaving system cuts hairs up to 30% closer

A comfortable shave

- Personalize your shave with three speed settings
- Get a comfortable dry or refreshing wet shave
- Lifts hairs to cut comfortably close

Get the most of your shaver

- SmartClean cleans, lubricates, dries and charges your shaver
- Click-on trimmer for perfect mustache and sideburn trimming
- Convenient travel case

Easy to use

- Intuitive icons make the functions easy to use
- 50 minutes cordless shaving after a one-hour charge
- Built to last, this shaver comes with a full 2 year warranty

PHILIPS


Features

Contour Detect Technology



Follow every contour of your face and neck with 8-directional ContourDetect technology. You'll catch 20% more hairs* in a single pass, resulting in an extremely close, smooth shave.

V-Track Precision Blades



The V-Track Precision Blades collect hair in the optimal cutting position, resulting in a more comfortable shave that's 30% closer*. The blades also self-sharpen to ensure a premium shave day after day.

Personal Comfort Settings



Customize your shave by choosing the speed setting that best fits you: Sensitive – for a gentle, yet thorough shave. Normal – for a thorough - everyday shave. Fast – for a quick shave that saves you time.

Shave Wet or Dry



Choose how you prefer to shave. Shave in the shower. Or use with water, foam, or gel for refreshing, comfortable shave.

SmartClean System



At the touch of a button, the SmartClean System cleans, lubricates, dries, and charges your shaver, keeping it performing at its best, day in and day out.

5 level LED display



The intuitive display shows relevant information, enabling you to get the best performance out of your shaver: - 5-level battery and travel lock indicators - Cleaning Indicator - Battery Low Indicator - Replacement Head Indicator

Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.

SmartClick Precision Trimmer



Click on our skin-friendly precision trimmer to finish your look. It's ideal for maintaining your mustache and trimming your sideburns.

50 minutes of cordless shaving



Shave longer with every charge, thanks to our powerful and long-lasting Lithium-ion battery. Do a quick charge for 5 minutes and you'll have enough power for one shave. All Shaver Series 9000 models are designed to operate only in cordless mode, to ensure you'll always be safe when shaving with water, even in the shower.

Travel case



The sleek design of the shaver storage case takes up less space and a built-in ventilation chamber dries your shaver even when you're on the go.

Full 2 Year Warranty



Philips backs this shaver with a 2-year guarantee. Our Series 9000 Shavers are designed for performance and durability, promising you an extremely close shave time after time.

Specifications

Please note that this is a pre-sales leaflet. The contents of this leaflet reflect the best of our knowledge per date and country mentioned above. The contents of this leaflet are subject to change without notice. Philips does not accept any liability as to the contents of this leaflet.

Shaving Performance

Contour following Shaving system 8-direction ContourDetectHeads V-Track Precision Blade System Super Lift & Cut Action
 Personal Comfort Settings Sensitive-Normal-Fast settings
 SkinComfort AquaTec Wet & Dry

Cleaning

Travel lock indicator Fully washable

Design

Color Handle

Glacier Blue Ergonomic grip & handling

Power

Battery Type Lithium-ion
 Run time 50 min / 17 shaves
 Charging 1 hour full charge Quick charge for 1 shave
 Automatic voltage 100-240 V
 Max power consumption 9 W
 Stand-by power 0.1 W

Accessories

SmartClean Cleans Lubricates Dries Charges Cleaning cartridge (included)
 SmartClick Precision trimmer
 Pouch Travel pouch

Service

2-year guarantee Yes
 Replacement head Replace every yr with SH90

Ease of use

Display 5 level battery indicator Battery low indicator Cleaning indicator Replace shaving heads indicator

* Cuts up to 20% more hair - versus SensoTouch



data subject to change 2019, October 8
 Version: 13.0.1
 UPC: 00075020041845

© 2019 Koninklijke Philips N.V. All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. or their respective owners.

www.philips.com