

PHILIPS

NORELCO

Wet and dry electric shaver

Shaver series 9000

V-Track Precision Blades

8-direction
ContourDetectHeads

SmartClean System



S9321/88



Perfection in every pass

Cuts up to 20% more hair* in a single pass

Our most advanced shaving system, the Series 9000 cuts hairs up to 30% closer to skin with its V-Track precision blades*. The shaving heads, with contour detect technology, move in 8 directions to cut up to 20% more hair in a single pass*.

Designed for perfection

- Uniquely designed shaving system cuts hairs up to 30% closer
- Heads move in 8 directions for an extremely close result

A comfortable shave

- Get a comfortable dry or refreshing wet shave
- Personalize your shave with three speed settings
- Lifts hairs to cut comfortably close

Get the most of your shaver

- Convenient travel case
- SmartClean cleans, lubricates, dries and charges your shaver
- Click-on trimmer for perfect mustache and sideburn trimming

Easy to use

- 50 minutes cordless shaving after a one-hour charge
- Built to last, this shaver comes with a full 2 year warranty


Highlights

Contour Detect Technology




Follow every contour of your face and neck with 8-directional ContourDetect technology. You'll catch 20% more hairs* in a single pass, resulting in an extremely close, smooth shave.

V-Track Precision Blades



The V-Track Precision Blades collect hair in the optimal cutting position, resulting in a more comfortable shave that's 30% closer*. The blades also self-sharpen to ensure a premium shave day after day.

Personal Comfort Settings



Customize your shave by choosing the speed setting that best fits you: Sensitive – for a gentle, yet thorough shave. Normal – for a thorough – everyday shave. Fast – for a quick shave that saves you time.

Shave Wet or Dry



Choose how you prefer to shave. Shave in the shower. Or use with water, foam, or gel for refreshing, comfortable shave.

SmartClean System



At the touch of a button, the SmartClean System cleans, lubricates, dries, and charges your shaver, keeping it performing at its best, day in and day out.

Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.

SmartClick Precision Trimmer



Click on our skin-friendly precision trimmer to finish your look. It's ideal for maintaining your mustache and trimming your sideburns.

50 minutes of cordless shaving



Shave longer with every charge, thanks to our powerful and long-lasting Lithium-ion battery. Do a quick charge for 5 minutes and you'll have enough power for one shave. All Shaver Series 9000 models are designed to operate only in cordless mode, to ensure you'll always be safe when shaving with water, even in the shower.



iF DESIGN AWARD 2015

Shaver series 9000Precision, control and maneuverability are the defining features of the 9000 shaver. The V-Track system guides hairs into the best cutting position for the closest result, while fully flexible eight directional heads catch more hairs for a clean shave in fewer strokes. The "AquaTec Wet & Dry" seal of this shaver allows for a comfortable dry shave or a refreshing wet shave, using a shaving gel or foam for extra skin comfort.

Specifications

Shaving Performance

Shaving system: V-Track Precision Blade System, Super Lift & Cut Action

Contour following: 8-direction ContourDetectHeads

SkinComfort: AquaTec Wet & Dry

Personal Comfort Settings: Sensitive-Normal-Fast settings

Accessories

SmartClean System: Charges, Cleaning cartridge (included), Cleans, Dries, Lubricates

SmartClick: Precision trimmer

Pouch: Travel pouch

Ease of use

Display: 5 level battery indicator, Cleaning indicator, Battery low indicator, Replace shaving heads indicator, Travel lock indicator

Cleaning: Fully washable

Design

Color: Argus

Handle: Ergonomic grip & handling

Power

Battery Type: Lithium-ion

Run time: 50 min / 17 shaves

Charging: Charge 1 hour for 50 min use, Quick charge for 1 shave

Automatic voltage: 100-240 V

Stand-by power: 0.1 W

Maximum power consumption: 9 W

Service

2-year guarantee

Replacement head: Replace every yr with SH90

Extra shaving head included: SH90

