

# PHILIPS

## NORELCO

Wet and dry electric shaver

Shaver series 9000

V-Track Precision Blades

8-direction  
ContourDetectHeads

SmartClean System

SmartClick beard styler



S9321/89



## Perfection in every pass

Cuts up to 20% more hair\* in a single pass

Our most advanced shaving system, the Series 9000 cuts hairs up to 30% closer to skin with its V-Track precision blades\*. The shaving heads, with contour detect technology, move in 8 directions to cut up to 20% more hair in a single pass\*.

### Designed for perfection

- Uniquely designed shaving system cuts hairs up to 30% closer
- Heads move in 8 directions for an extremely close result

### A comfortable shave

- Get a comfortable dry or refreshing wet shave
- Personalize your shave with three speed settings
- Lifts hairs to cut comfortably close

### Get the most of your shaver

- Convenient travel case
- SmartClean cleans, lubricates, dries and charges your shaver
- Click-on beard styler with 5 length settings

### Easy to use

- 50 minutes cordless shaving after a one-hour charge
- Built to last, this shaver comes with a full 2 year warranty


# Highlights

## Contour Detect Technology




Follow every contour of your face and neck with 8-directional ContourDetect technology. You'll catch 20% more hairs\* in a single pass, resulting in an extremely close, smooth shave.

## V-Track Precision Blades



The V-Track Precision Blades collect hair in the optimal cutting position, resulting in a more comfortable shave that's 30% closer\*. The blades also self-sharpen to ensure a premium shave day after day.

## Personal Comfort Settings



Customize your shave by choosing the speed setting that best fits you: Sensitive – for a gentle, yet thorough shave. Normal – for a thorough – everyday shave. Fast – for a quick shave that saves you time.

## Shave Wet or Dry



Choose how you prefer to shave. Shave in the shower. Or use with water, foam, or gel for refreshing, comfortable shave.

## SmartClean System



At the touch of a button, the SmartClean System cleans, lubricates, dries, and charges your shaver, keeping it performing at its best, day in and day out.

## Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.

## SmartClick beard styler



Change your look with the SmartClick Beard Styler attachment. Choose from 5 length settings to create anything from a perfect stubble look to a short, neatly trimmed beard. Rounded tips and combs are designed to prevent skin irritation.

## 50 minutes of cordless shaving



Shave longer with every charge, thanks to our powerful and long-lasting Lithium-ion battery. Do a quick charge for 5 minutes and you'll have enough power for one shave. All Shaver Series 9000 models are designed to operate only in cordless mode, to ensure you'll always be safe when shaving with water, even in the shower.

## Travel case



The sleek design of the shaver storage case takes up less space and a built-in ventilation chamber dries your shaver even when you're on the go.

# Specifications

## Shaving Performance

**Shaving system:** V-Track Precision Blade System, Super Lift & Cut Action

**Contour following:** 8-direction ContourDetectHeads

**SkinComfort:** AquaTec Wet & Dry

**Personal Comfort Settings:** Sensitive-Normal-Fast settings

## Accessories

**SmartClean System:** Charges, Cleaning cartridge (included), Cleans, Dries, Lubricates

**SmartClick:** Beard styler

**Pouch:** Travel pouch

## Ease of use

**Display:** 5 level battery indicator, Cleaning indicator, Battery low indicator, Replace shaving heads indicator, Travel lock indicator

**Cleaning:** Fully washable

## Design

**Color:** Argus

**Handle:** Ergonomic grip & handling

## Power

**Battery Type:** Lithium-ion

**Run time:** 50 min / 17 shaves

**Charging:** Rechargeable, Charge 1 hour for 50 min use, Quick charge for 1 shave

**Automatic voltage:** 100-240 V

**Stand-by power:** 0.1 W

**Maximum power consumption:** 9 W

## Service

**2-year guarantee**

**Replacement head:** Replace every yr with SH90

