

PHILIPS

NORELCO

Wet & dry electric
shaver, Series 9000

Shaver 9500

V-Track Precision Blades

8-direction
ContourDetectHeads

Motion Sensor Display



S9531/83



Perfection in every pass

Cuts up to 20% more hair* in a single pass

Our most advanced shaving system, the Series 9000 cuts hairs up to 30% closer to skin with its V-Track precision blades*. The shaving heads, with contour detect technology, move in 8 directions to cut up to 20% more hair in a single pass*.

Designed for perfection

- Uniquely designed shaving system cuts hairs up to 30% closer
- Heads move in 8 directions for an extremely close result

A comfortable shave

- Get a comfortable dry or refreshing wet shave
- Personalize your shave with three speed settings
- Lifts hairs to cut comfortably close

Get the most of your shaver

- Click-on trimmer for perfect mustache and sideburn trimming
- Convenient travel case

Easy to use

- 50 minutes cordless shaving after a one-hour charge
- Built to last, this shaver comes with a full 2 year warranty
- 5-level battery and travel lock Indicators

Highlights

50 minutes of cordless shaving



Shave longer with every charge, thanks to our powerful and long-lasting Lithium-ion battery. Do a quick charge for 5 minutes and you'll have enough power for one shave. All Shaver Series 9000 models are designed to operate only in cordless mode, to ensure you'll always be safe when shaving with water, even in the shower.

Travel case



The sleek design of the shaver storage case takes up less space and a built-in ventilation chamber dries your shaver even when you're on the go.

Full 2 Year Warranty



Philips backs this shaver with a 2-year guarantee. Our Series 9000 Shavers are designed for performance and durability, promising you an extremely close shave time after time.

LED User Interface




The intuitive display shows relevant information, enabling you to get the best performance out of your shaver: - 5-level Battery Indicator - Cleaning Indicator - Battery Low Indicator - Replacement Head Indicator - Travel Lock Indicator

SmartClick Precision Trimmer



Click on our skin-friendly precision trimmer to finish your look. It's ideal for maintaining your mustache and trimming your sideburns.

Personal Comfort Settings




Customize your shave by choosing the speed setting that best fits you: Sensitive – for a gentle, yet thorough shave. Normal – for a thorough - everyday shave. Fast – for a quick shave that saves you time.

Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.

V-Track Precision Blades



The V-Track Precision Blades collect hair in the optimal cutting position, resulting in a more comfortable shave that's 30% closer*. The blades also self-sharpen to ensure a premium shave day after day.

Contour Detect Technology



Follow every contour of your face and neck with 8-directional ContourDetect technology. You'll catch 20% more hairs* in a single pass, resulting in an extremely close, smooth shave.

Specifications

Shaving Performance

Shaving system: V-Track Precision Blade System, Super Lift & Cut Action

Contour following: 8-direction ContourDetectHeads

SkinComfort: AquaTec Wet & Dry

Personal Comfort Settings: Sensitive-Normal-Fast settings

Accessories

SmartClean PLUS: Cleans, Dries, Charges, Lubricates, Cleaning cartridge (included)

SmartClick: Precision trimmer

Pouch: Travel pouch

Ease of use

Display: 5 level battery indicator, Battery low indicator, Cleaning indicator, Replace shaving heads indicator, Travel lock indicator

Cleaning: Fully washable

Design

Color: Black HG

Handle: Ergonomic grip & handling

Power

Charging: 1 hour full charge, Quick charge for 1 shave

Battery Type: Lithium-ion

Run time: 50 min / 17 shaves

Automatic voltage: 100-240 V

Stand-by power: 0.1 W

Max power consumption: 9 W

Service

2-year guarantee

Replacement head: Replace every yr with SH90

