

# PHILIPS

## NORELCO

Wet & dry electric  
shaver, Series 9000

Shaver 9500

V-Track Precision Blades

8-direction  
ContourDetectHeads

SmartClean System

Motion Sensor Display



S9531/84



## Perfection in every pass

Cuts up to 20% more hair\* in a single pass

Our most advanced shaving system, the Series 9000 cuts hairs up to 30% closer to skin with its V-Track precision blades\*. The shaving heads, with contour detect technology, move in 8 directions to cut up to 20% more hair in a single pass\*.

### Designed for perfection

- Heads move in 8 directions for an extremely close result
- Uniquely designed shaving system cuts hairs up to 30% closer

### A comfortable shave

- Personalize your shave with three speed settings
- Get a comfortable dry or refreshing wet shave
- Lifts hairs to cut comfortably close

### Get the most of your shaver

- SmartClean cleans, lubricates, dries and charges your shaver
- Click-on trimmer for perfect mustache and sideburn trimming
- Convenient travel case

### Easy to use

- 5-level battery and travel lock Indicators
- 50 minutes cordless shaving after a one-hour charge
- Built to last, this shaver comes with a full 2 year warranty



asimpleswitch.com


# Highlights

## Contour Detect Technology




Follow every contour of your face and neck with 8-directional ContourDetect technology. You'll catch 20% more hairs\* in a single pass, resulting in an extremely close, smooth shave.

## V-Track Precision Blades



The V-Track Precision Blades collect hair in the optimal cutting position, resulting in a more comfortable shave that's 30% closer\*. The blades also self-sharpen to ensure a premium shave day after day.

## Personal Comfort Settings



Customize your shave by choosing the speed setting that best fits you: Sensitive – for a gentle, yet thorough shave. Normal – for a thorough – everyday shave. Fast – for a quick shave that saves you time.

## LED User Interface



The intuitive display shows relevant information, enabling you to get the best performance out of your shaver: - 5-level Battery Indicator - Cleaning Indicator - Battery Low Indicator - Replacement Head Indicator - Travel Lock Indicator

## Shave Wet or Dry



Choose how you prefer to shave. Shave in the shower. Or use with water, foam, or gel for refreshing, comfortable shave.

## SmartClean System



At the touch of a button, the SmartClean System cleans, lubricates, dries, and charges your shaver, keeping it performing at its best, day in and day out.

## Super Lift & Cut Action



Shave closer with the dual-blade Super Lift & Cut Action. The first blade raises each hair while the second blade comfortably cuts below skin level, for exceptionally smooth results.

## IF DESIGN AWARD 2015

Shaver series 9000 Precision, control and maneuverability are the defining features of the 9000 shaver. The V-Track system guides hairs into the best cutting position for the closest result, while fully flexible eight directional heads catch more hairs for a clean shave in fewer strokes. The "AquaTec Wet & Dry" seal of this shaver allows for a comfortable dry shave or a refreshing wet shave, using a shaving gel or foam for extra skin comfort.



[asimpleswitch.com](http://asimpleswitch.com)

## Philips Green Logo

Philips Green Products can reduce costs, energy consumption and CO2 emissions. How? They offer a significant environmental improvement in one or more of the Philips Green Focal Areas – Energy efficiency, Packaging, Hazardous substances, Weight, Recycling and disposal and Lifetime reliability.

# Specifications

## Shaving Performance

**Shaving system:** V-Track Precision Blade System, Super Lift & Cut Action

**Contour following:** 8-direction ContourDetectHeads

**Personal Comfort Settings:** Sensitive-Normal-Fast settings

**SkinComfort:** AquaTec Wet & Dry

## Accessories

**SmartClick:** Precision trimmer

**Pouch:** Travel pouch

**SmartClean PLUS:** Cleans, Lubricates, Dries, Charges, Cleaning cartridge (included)

## Ease of use

**Display:** 5 level battery indicator, Battery low indicator, Cleaning indicator, Replace shaving heads indicator, Travel lock indicator

**Cleaning:** Fully washable

## Design

**Color:** Black HG

**Handle:** Ergonomic grip & handling

## Power

**Battery Type:** Lithium-ion

**Run time:** 50 min / 17 shaves

**Charging:** 1 hour full charge, Quick charge for 1 shave

**Automatic voltage:** 100-240 V

**Max power consumption:** 9 W

**Stand-by power:** 0.1 W

## Service

**2-year guarantee**

**Replacement head:** Replace every yr with SH90

