

# PHILIPS

Wet and dry electric shaver

Shaver series 9000

V-Track blade system PRO

8 direction ContourDetect Heads

SmartClean System Plus

SmartClick beard styler



S9711/31



## Perfection in every pass

Cuts up to 20% more hair\* in a single pass

The Shaver 9000 is our most advanced shaver yet. The unique contour-detect technology offers exceptional coverage over every contour of your face, and the V-Track system guides hairs into the best cutting position for the closest shave.

### Designed for perfection

- Our best shaving system on 1–3-day beards
- Heads flex in 8 different directions for a superb result

### A comfortable shave

- Personalise your shave by choosing between three settings
- Get a comfortable dry or refreshing wet shave with Aquatec

### Easy to use

- Intuitive icons make the functions easy to use
- 60 minutes cordless shaving after a one-hour charge
- Shaver can be rinsed clean under the tap
- With 2 year guarantee


### Get the most of your shaver

- Keep your shaver in great condition with SmartClean
- Click-on beard styler with 5 length settings



# Highlights

## V-Track blade system PRO




Get the perfect close shave. The V-Track Precision PRO Blades gently position each hair in the best cutting position, from 1-day to 3-day beards, including flat-lying hairs and hairs of different lengths. Cuts 30% closer\* in fewer strokes, leaving your skin in great condition.

## 8 direction ContourDetect Heads



Follow every contour of your face and neck with 8 directional ContourDetect heads. You'll catch 20% more hairs with every pass, resulting in an extremely close, smooth shave.

## Personal comfort settings



Choose between 3 modes to customise your shave: Sensitive — for a gentle yet thorough shave. Normal — for a thorough, everyday shave. Fast — for a quick shave that saves you time.

## Aquatec Wet & Dry



Choose how you prefer to shave. With the Aquatec Wet & Dry seal, you can opt for a quick-yet-comfortable dry shave. Or you can shave wet – with gel or foam – even in the shower.

## SmartClean System PLUS



At the touch of a button SmartClean PLUS cleans, lubricates, dries and charges your shaver, so it'll perform at its best every day.

## SmartClick beard styler



Change your look with the SmartClick Beard Styler attachment. Choose from 5 length settings to create anything from a perfect stubble look to a short, neatly trimmed beard. Rounded tips and combs are designed to prevent skin irritation.

## Digital display



The intuitive display shows relevant information, enabling you to get the best performance out of your shaver: - 3 digit (%) battery indicator - Cleaning Indicator - Battery Low Indicator - Replacement Head Indicator - Travel Lock Indicator.

## 60 minutes of cordless shaving



Now with the most superior battery life of all Philips Shavers, the charging system gives you two convenient options: 60 minutes of running time after a single one-hour charge, or quick charge for one full shave. All Shaver series 9000 models are designed to operate only in cordless mode to ensure safety in wet environments.



**IF DESIGN AWARD 2015**  
Shaver series 9000iF DESIGN AWARD 2015

# Specifications

## Shaving Performance

**Shaving system:** V-Track blade system PRO  
**Contour following:** 8 direction ContourDetect Heads

**SkinComfort:** Aquatec Wet and Dry

**Personal Comfort Settings:** Sensitive-Normal-Fast settings

## Accessories

**SmartClick:** Beard styler

**SmartClean PLUS:** Cleans, Lubricates, Dries, Charges, Cleaning cartridge (included)

**Pouch:** Travel pouch

## Ease of use

**Display:** % Battery Level Indicator, Cleaning indicator, Battery low indicator, Replace shaving heads indicator, Travel lock indicator

**Cleaning:** Fully washable

## Design

**Colour:** Brushed chrome

**Handle:** Ergonomic grip and handling

## Power

**Battery Type:** Lithium-ion

**Run time:** 60 min (20 shaves)

**Charging:** 1 hour full charge, Quick charge for 1

shave

**Automatic voltage:** 100-240 V

**Max power consumption:** 9 W

**Stand-by power:** 0.1 W

## Service

**2 year guarantee**

**Replacement head:** Replace every 2 yrs with SH90

## FK-PC-Shavers

Wet and Dry

