



Philips GoGEAR
MP3 player

2 GB*

GoGEAR

SA018102S



More music, superior sound

with FullSound™ and FM radio

The ultra compact and wearable Philips GoGear SA018 MP3 player comes equipped with FullSound™ to bring MP3 music to life. For more music options, there's FM radio... and it's all presented in a sleek and seamless stainless steel design.

For superb music enjoyment

- FullSound™ to bring your MP3 music to life
- Shuffle to mix up your songs and be surprised everytime
- Up to 12 hours MP3 and WMA music playback plus FM radio

Ready to wear, ready to go

- Small and stylish — like a fashion accessory
- Built-in clip for easy wear
- Brushed stainless steel body - sturdy and stylish

Easy and intuitive music experience

- Drag and drop your songs easily — no software needed
- Direct charging from PC via USB

PHILIPS

MP3 player
2 GB*

Specifications

Sound

- Frequency response: 20 - 18 k Hz
- Signal to noise ratio: > 84 dB
- Channel separation: 45 dB
- Output Power: 2 x 2.4 mW
- THD: 0.05% at 1 kHz
- Sound Enhancement: FullSound

Audio Playback

- Compression format: MP3, WMA
- MP3 bit rates: 8-320 kbps and VBR
- WMA bit rates: 5-320 kbps
- WMA sample rates: 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz
- MP3 sample rates: 16, 32, 44.1, 48, 11.025, 22.050, 24, 8 kHz

Storage Media

- Built-in memory type: NAND Flash
- Built-in memory (RAM): 2 GB
- Music memory capacity, MP3: Up to 450 tracks*
- Mass storage class compliant

Connectivity

- Headphones: 3.5 mm

Convenience

- Battery low indication
- Function: Keypad lock
- Volume control
- Firmware upgradeable



Accessories

- Headphones: AY3819
- Quick start guide
- USB cable

Software

- Device manager: to restore and upgrade

Green Specifications

- Lead-free soldered product

System Requirements

- PC OS: Windows 2000/XP/Vista
- Internet connection: Yes (for access to updated support documents, manuals, future firmware and PC software upgrades)
- USB: Free USB port

Power

- Play time on internal battery: Up to 12 hours
- Battery Type: Li-Polymer
- Rechargeable: Yes, via USB

Dimensions

- Product dimensions (WxDxH): 47 x 13 x 23 mm
- Packaging type: Jewel box

Tuner/Reception/Transmission

- Station presets: 5
- Tuner Bands: FM

SA018102S/02

Highlights

FullSound™

Philips' innovative FullSound technology faithfully restores sonic details to compressed MP3 music, dramatically enriching and enhancing it, so you can experience CD music without any distortion. Based on an audio post-processing algorithm, FullSound combines Philips' renowned expertise in music reproduction with the power of the latest generation Digital Signal Processor (DSP). The result is fuller bass with more depth and impact, boosted voice and instrument clarity, and rich detail. Rediscover your compressed MP3 music in true-to-life sound that will touch your soul and move your feet.



Issue date 2015-11-30

Version: 1.0.4

12 NC: 8670 000 56731
EAN: 87 12581 50858 6

© 2015 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.

* Actual transfer speed may vary based on your operating system and software configuration.

* 1 GB = 1 billion bytes; available storage capacity will be less.

* Rechargeable batteries have a limited number of charge cycles and may eventually need to be replaced. Battery life and number of charge cycles vary by use and settings.

* From Philips