



Philips GoGEAR  
MP3 video player

8GB\*

GoGEAR

SA075108K

## Superior sound experience

with high definition video playback

The SA075 puts lively TV into your hands. Watch popular formats like RMVB, MPEG4 or AVI, in high definition (720p). A 10.9cm/4.3" touchscreen and dual built-in speakers add to viewing pleasure. Also enjoy HD video on TV via HDMI connection.

### Superb quality sound

- Fullsound™ to bring your MP3 music to life
- 2 built-in speakers for powerful sound
- FLAC & APE lossless codec support for precise sound quality

### Complements your life

- 4.3" WVGA color LCD display for superb video experience
- HDMI out to watch High Definition (720p) video on HDTV
- Supports 720P RMVB, MPEG4, and AVI for video playback
- FM radio with 20 presets for more music options
- Up to 20-hour music or 3-hour video playback

### Easy and intuitive

- Touch-screen control for smooth and intuitive navigation
- Kinetic scrolling for quick and intuitive library browsing
- microSD card slot for expanded memory capacity
- Text reader to view text files

# PHILIPS

# Specifications

## Picture/Display

- Backlight
- Diagonal screen size (inch): 4.3 inch
- Type: LCD Touch-sensitive screen
- Resolution: WVGA, 800 x 480 pixels, 16M colours

## Sound

- Equalizer customizable
- Frequency response: 45 - 18k Hz
- Equalizer settings: Hip Hop, Jazz, Pop, Rock, Classical
- Output Power: 2 x 10mW
- Signal to noise ratio: > 80 dB
- THD: 0.05% at 1kHz
- Sound Enhancement: FullSound
- Channel separation: 45 dB

## Audio Playback

- Compression format: MP3, WMA, AAC, FLAC, APE
- ID3 Tag support: Song title, artist, album
- MP3 bit rates: 8-320 kbps and VBR
- WMA bit rates: 5-192 kbps
- WMA sample rates: 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz
- MP3 sample rates: 16, 32, 44.1, 48, 11.025, 22.050, 24, 8 kHz
- Lyrics support: .lrc file

## Still Picture Playback

- Picture Compression Format: JPEG, BMP
- Slide show

## Storage Media

- Built-in memory type: NAND Flash
- Mass storage class compliant
- Built-in memory (RAM): 8 GB
- External Storage: Micro SD memory card slot

## Connectivity

- Headphone: 3.5 mm
- USB: High speed USB 2.0

## Convenience

- Battery low indication
- Function: Keypad lock
- Volume control

- Firmware upgradeable
- Battery charging indication: On User Interface

## Accessories

- Headphones: AY3816
- USB cable: AY3930
- Quick start guide

## Software

- Device manager: to restore and upgrade

## Green Specifications

- Lead-free soldered product

## System Requirements

- PC OS: Windows XP (SP2) or Windows Vista
- Internet connection: Yes (for access to updated support documents, manuals, future firmware and PC software upgrades)
- USB: Free USB port

## Power

- Battery capacity: 1350 mAh
- Playtime on internal battery: Up to 20 hours audio, or 3.5 hours video
- Battery Type: LI-Polymer
- Rechargeable: Yes, via USB

## Dimensions

- Box dimensions (W x H x D): 140 x 133 x 42 mm
- Packaging type: D-box
- Product dimensions (WxDxH): 135 x 12 x 76 mm
- Product weight: 0.126 kg

## Tuner/Reception/Transmission

- Tuner Bands: FM
- Station presets: 20

## Video Playback

- RMVB: Up to 2Mbps in rm/rmvb format, 1280x720, 25fps
- MPEG4 SP: Up to 2Mbps in avi/mp4 format, 1280x720p, 30fps
- Video/ Picture output to TV: HDMI

## Audio Capturing

- FM radio recording



Issue date 2014-02-12

Version: 1.0.6

12 NC: 8670 000 60925  
EAN: 87 12581 53052 5

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)