


Digital audio player



3 in one

- Digital FM tuner
- One touch digital voice memo recording
- Upgradeable/ Futureproof
- Graphical LCD display with a Tri-colour backlight
- MMC/SD Memory expansion slot (supports upto 128MB card)
- MP3 & Windows Media Audio playback
- Built-in 64MB memory
- 100% Shockproof
- 6 preset EQ & a custom setting
- Ultra compact size



RUSH!

Let's make things better.



PHILIPS

Digital audio player



Standard product information

Amplifier/ system

- Output power 2 x 5mW
- EQ sound processing
- Digital volume control
- S/N ratio (A weighted) >80 dB
- Frequency response 20 Hz - 20 kHz

Digital audio player

- Shuffle, repeat one and repeat all
- Search forward/backward with rapid advance
- Hold

Display

- Graphical LCD display with a Tri-colour backlight
- Displays track number, time, title & artist
- Indication for volume level, play mode, and battery level

Connections

- Headphone/ line out Stereo, 3.5 mm
- I/O Interface 5-pin mini-USB connector

Power supply

- Battery 1 x 1.5 V, type AAA/LR03
- Battery playing time 9 hours (Alkaline battery)
- Automatic power switch-off

General

- Case material High temperature resistant plastic top, & bottom
- Weight 50 g (excluding battery)
- Product dimensions (mm) 55 W x 76 H x 21 D
- D-box dimensions /00c (mm) 225 W x 164 H x 71 D
- Master carton dimensions /00c (mm) 225 W x 330 H x 142 D
- Master carton quantity 4

Accessories

- USB port cable
- Bass wave in-ear headphone
- Arm band
- Necklace strap
- AAA Alkaline battery
- CD Rom

Digital FM tuner

FM tuning (87.5 - 108MHz) with 10 presets.

One Touch digital voice recording

Make multiple voice memo recordings, useful for meetings and important discussions. Provides upto 4hrs of digital voice recording capacity when using the full 64MB* internal memory and even more recording capacity when using a MMC/SD memory card. (*Some memory will be used by the device).

Upgradeable/ futureproof

This futureproof technology for digital audio players allows users to upgrade the playback software in their player to accommodate new audio compression standards.

Multi-line graphical LCD display with tri-color backlight

Multi-line graphical LCD display with a unique function specific color back light (orange for digital audio, green for FM radio; red for voice) to aid navigation in the dark.

Memory expansion slot

Supports MMC/SD memory card types to extend the memory size upto 192MB. (Note: Support for higher capacity cards via future firmware upgrades).

mp3/ wma/ wav playback

Currently supports mp3 and windows media audio (wma) file format playback in music and .wav only in voice memo playback modes.

Built-in 64MB flash memory

Built in 64MB* to provide upto 90 mins of near CD quality mp3 music (@ 96Kbps bitrate) or 180min of wma music (@ 48kbps). (*Some memory will be used by the device).

100% Shockproof

100% guaranteed no skip protection for continuous music play.

6 preset EQ and a Custom setting

Two bass setting to give deep rich bass sounds, other equalizer functions such Rock, Pop, Jazz, Classic and a custom setting to allow the user to define an equalizer setting.

Ultra compact size

Highly integrated unit minimising size and bringing the best in portability.

Automatic power off

Automatically switches off the player if it is not actively being used.

My Favourite

My Favourite provides the means of creating your own favorite play list and play the list in the chosen playmode.

Hold

Locks all buttons to prevent interruption of play or change of program settings.

Next/ previous

Plays the next or previous track at the touch of a button.

Shuffle

Plays track selection randomly, giving you each time a new sequence of tracks.

Repeat one/ all

Repeat the current track or the total tracks.

3 play modes

Let you enjoy various play modes (repeat one/ repeat all/ shuffle).

Printed in Hong Kong 2002-07-29
Specifications subject to modification without notice
2002 © Koninklijke Philips Electronics N.V.
All rights reserved

www.philips.com
www.audio.philips.com

Let's make things better.



PHILIPS