




Philips GoGEAR
MP4 player with
FullSound™

Ariaz
4GB*

GoGEAR



SA2ARA04KN

Superior sound experience

And enjoy all the multimedia you can pack in

Tune in to GoGear Ariaz with FullSound™ and sound isolation headphones for exceptional sound on the go. Enjoy entertainment galore with its 2.4" screen, Philips Songbird, and superbly long music (45 hours) and video (5 hours) playback.

Superb quality sound

- Fullsound™ to bring your MP3 music to life
- Sound Isolation headphones to minimize environmental noise

Complements your life

- Audible.com features digital audiobooks and more
- 6.1 cm (2.4") full color display for fantastic video quality
- Up to 45-hour music or 5-hour video playback
- Voice recording to take notes or record anything, anytime

Easy and intuitive


- Smart Shuffle to listen to what you like most first
- Folder view to organize and view media files like on your PC

PHILIPS

MP4 player
Ariaz 4GB*

Highlights

FullSound™



Philips' innovative FullSound technology faithfully restores sonic details to compressed MP3 music, dramatically enriching and enhancing it, so you can experience CD music without any distortion. Based on an audio post-processing algorithm, FullSound combines Philips' renowned expertise in music reproduction with the power of the latest generation Digital Signal Processor (DSP). The result is fuller bass with more depth and impact, boosted voice and instrument clarity, and rich detail. Rediscover your compressed MP3 music in true-to-life sound that will touch your soul and move your feet.

Audible



Audible.com is your destination for the widest selection of digital audiobooks, magazines, radio shows, stand-up comedy, and more available for download. Enjoy books in the car, at the gym, or around the house. Authors and icons read their own works, and famous actors narrate your favorite titles. At Audible.com you can browse and sample over 75,000 selections, including the latest best sellers and timeless classics.

Sound isolation headphones



With sound isolation headphones, you will hear greater music details at a lower volume than is possible with normal headphones. Based on thorough understanding of the human ear canal anatomy, the sound isolation headphone's angled acoustic design creates a perfect seal between the ambient sound source & the ear canal, thus eliminating unwanted background noise while delivering sound directly to your ears. Even at a moderate volume setting, you can still discern music details without noise distractions from the environment. Earphone sleeves are available in three sizes to provide the best fit.

6.1 cm/2.4" full color display




A cool 6.1 cm (2.4") high resolution display on your GoGear player offers excellent video quality and crisp, vivid images. Together with a full color menu, the large screen allows easy navigation of media files to complete the package for a all-round multimedia experience on the go.

SA2ARA04KN/55

45-hour music/5-hour video

Forget about the hassle of having to recharge your GoGear player battery constantly. This extremely long lasting player allows you to savor your favorite tunes for up to a whopping 45 hours of continuous music playback or up to 5 hours of video playback - all on a single charge. Now you can sit back and listen to music all day long or watch the equivalent of 3 movies back-to-back wherever you go.

Smart Shuffle



Smart Shuffle

Smart Shuffle to listen to what you like most first

Voice recording



Voice recording converts your GoGear player into a handy dictation machine. Besides playing music or listening to radio, you can also record notes or reminders for work or school, record shopping lists and phone numbers – even song lyrics. By pressing the recording button and speaking into the built-in microphone, voice messages are compressed and stored in the built-in internal memory. Voice recording gives you a highly portable voice recorder allowing you to record anything, anytime and anywhere!



AudibleReady

Specifications

Picture/Display

- Backlight
- Type: LCD
- Diagonal screen size (inch): 2.4 inch
- Resolution: 320 x 240 pixels
- Diagonal screen size (cm): 6.10 cm

Sound

- Equalizer customizable
- Equalizer settings: FullSound, Funk, Hip Hop, Jazz, Rock, Techno, Classical
- Frequency response: 20 - 18 000 Hz
- Signal to noise ratio: > 84 dB
- Channel separation: 45 dB
- Sound Enhancement: FullSound
- Output power (RMS): 2 x 2.4 mW

Audio Playback

- Compression format: MP3, WAV, WMA, FLAC, APE
- ID3 Tag support: Song title, artist, album
- MP3 bit rates: 8-320 kbps and VBR
- WMA bit rates: 5-320 kbps
- WMA sample rates: 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz
- MP3 sample rates: 16, 32, 48, 11.025, 22.050, 8 kHz
- Digital Rights Management: Windows Media DRM for Portable Devices, Supports download & subscription music services

Still Picture Playback

- Picture Compression Format: JPEG, BMP
- Slide show

Storage Media

- Built-in memory type: NAND Flash
- Mass storage class compliant
- Built-in memory (RAM): 4 GB
- Music memory capacity, MP3: Up to 900 tracks*

Connectivity

- Headphone: 3.5 mm
- USB: USB 2.0

Convenience

- Dedicated volume controls
- Function: Keypad lock
- Superscroll
- Firmware upgradeable

- Battery charging indication: On user interface
- Charge & play: when connected to PC
- Customizable volume limit

Accessories

- Headphones: AY3834
- USB cable: AY3930
- Quick start guide

Software

- Philips Songbird

Green Specifications

- Lead-free soldered product
- Certified green product: pending

System Requirements

- CD-ROM drive
- PC OS: Windows XP (SP3) / Windows Vista / Windows 7
- Internet connection: Yes (for access to updated support documents, manuals, future firmware and PC software upgrades)
- USB: Free USB port

Power

- Battery capacity: 560 mAh
- Battery Type: LI-Polymer
- Playtime on internal battery: Up to 45 hours audio or 5 hours video
- Rechargeable: Yes, via USB

Dimensions

- Packaging type: D-box
- Product dimensions (WxDxH): 92.0 x 8.9 x 52.0
- Product weight: 0.091 kg
- D-box dimensions (WxDxH): 140 x 30 x 120 mm

Video Playback

- WMV9: 320 x 240, 30 fps, 512 kbps

Audio Capturing

- Built-in microphone: mono
- Voice recording

Partners

- 7digital
- Audible



Issue date 2016-10-19

Version: 2.0.1

12 NC: 8670 000 67494
EAN: 87 12581 56219 9

© 2016 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.
* Actual transfer speed may vary based on your operating system and software configuration.
* 1GB = 1 billion bytes; available storage capacity will be less.
* Avoid extensive use of the set in a volume higher than 85 decibel because this may damage your hearing.