




Philips GoGEAR
MP4 player with
FullSound™

Ariaz
8 GB*

GoGEAR



SA2ARA08K

Superior sound experience

And enjoy all the multimedia you can pack in

Tune in to GoGear Ariaz with FullSound™ and sound isolation headphones for exceptional sound on the go. Enjoy entertainment galore with its 2.4" screen, Philips Songbird and superbly long music (45 hours) and video (5 hours) playback.

Superb quality sound

- FullSound™ to bring your MP3 music to life
- Sound Isolation headphones to minimise environmental noise

Complements your life

- Audible.com features digital audiobooks and more
- 6.1 cm (2.4") full colour display for fantastic video quality
- Up to 45-hour music or 5-hour video playback
- FM radio with RDS and 20 presets for more music options
- Voice recording to take notes or record anything, anytime

Easy and intuitive


- Smart Shuffle to listen to what you like most first
- Folder view to organise and view media files as you do on your PC

PHILIPS

MP4 player
Ariaz 8 GB*

Highlights

FullSound™



Philips' innovative FullSound technology faithfully restores sonic details to compressed MP3 music, dramatically enriching and enhancing it, so you can experience CD music without any distortion. Based on an audio post-processing algorithm, FullSound combines Philips' renowned expertise in music reproduction with the power of the latest generation Digital Signal Processor (DSP). The result is fuller bass with more depth and impact, boosted voice and instrument clarity, and rich detail. Rediscover your compressed MP3 music in true-to-life sound that will touch your soul and move your feet.

Audible



Audible.com is your destination for the widest selection of digital audiobooks, magazines, radio shows, stand-up comedy and more available for download. Enjoy books in the car, at the gym or around the house. Authors and icons read their own works, and famous actors narrate your favourite titles. At Audible.com you can browse and sample over 75,000 selections, including the latest bestsellers and timeless classics.

Sound isolation headphones



With sound isolation headphones, you will hear greater music details at a lower volume than is possible with normal headphones. Based on thorough understanding of the human ear canal anatomy, the sound isolation headphone's angled acoustic design creates a perfect seal between the ambient sound source and the ear canal, thus eliminating unwanted background noise while delivering sound directly to your ears. Even at a moderate volume setting, you can still discern music details without noise distractions from the environment. Earphone sleeves are available in three sizes to provide the best fit.

6.1 cm/2.4" full colour display



A cool 6.1 cm (2.4") high-resolution display on your GoGear player offers excellent video quality and crisp, vivid images. Together with a full colour menu, the large screen allows easy navigation of media files to complete the package for an all-round multimedia experience on the go.

45-hour music/5-hour video

Forget about the hassle of having to recharge your GoGear player battery constantly. This

SA2ARA08K/02


extremely long lasting player allows you to savour your favourite tunes for up to a whopping 45 hours of continuous music playback or up to 5 hours of video playback - all on a single charge. Now you can sit back and listen to music all day long or watch the equivalent of 3 movies back-to-back wherever you go.

FM radio with RDS/20 presets



RDS (Radio Data System) is a communications protocol standard that allows digital information to be transmitted over FM radio broadcasts. RDS-enabled FM radio receivers can display useful information including station identity, programme details and song title and artist etc. You can store a desired station as a preset channel on your GoGear player at any time. With the ability to store 20 preset radio stations, you can quickly access your favourite radio station without having to tune the frequencies manually each time.

Smart Shuffle



SmartShuffle

Smart Shuffle to listen to what you like most first



AudibleReady™

Specifications

Picture/Display

- Backlight
- Type: LCD
- Diagonal screen size (cm): 6.10 cm
- Diagonal screen size (inch): 2.4 inch
- Resolution: 320 x 240 pixels

Sound

- Equalizer customisable
- Equalizer settings: FullSound, Funk, Hip Hop, Jazz, Rock, Techno, Classical
- Sound Enhancement: FullSound
- Channel separation: 45 dB
- Frequency response: 20 - 18,000 Hz
- Output power (RMS): 2 x 2.4 mW
- Signal to noise ratio: > 84 dB

Audio Playback

- Compression format: MP3, WAV, WMA, FLAC, APE
- ID3 Tag support: Song title, artist, album
- MP3 sample rates: 16, 32, 48, 11.025, 22.050, 8 kHz
- Digital Rights Management: Windows Media DRM for Portable Devices, Supports download and subscription music services
- MP3 bit rates: 8-320 kbps and VBR
- WMA bit rates: 5-320 kbps
- WMA sample rates: 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz

Still Picture Playback

- Picture Compression Format: JPEG, BMP
- Slideshow

Storage Media

- Built-in memory type: NAND Flash
- Mass storage class compliant
- Built-in memory (RAM): 8 GB
- Music memory capacity, MP3: Up to 1800 tracks*

Connectivity

- Headphones: 3.5 mm
- USB: USB 2.0

Convenience

- Function: Keypad lock
- Superscroll
- Firmware upgradeable
- Battery charging indication: On user interface
- Charge and play: when connected to a PC
- Customisable volume limit
- Dedicated volume controls

Accessories

- Headphones: AY3834
- Quick start guide
- USB cable: AY3930

Software

- Philips Songbird

Green Specifications

- Lead-free soldered product
- Certified green product: pending

System Requirements

- CD-ROM drive
- USB: Free USB port
- Internet connection: Yes (for access to updated support documents, manuals, future firmware and PC software upgrades)
- PC OS: Windows XP (SP3)/Windows Vista/Windows 7

Power

- Battery Type: LI-Polymer
- Rechargeable: Yes, via USB
- Battery capacity: 560 mAh
- Play time on internal battery: Up to 45 hours of audio or 5 hours of video

Dimensions

- Packaging type: D-box
- D-box dimensions (WxDxH): 140 x 30 x 120 mm
- Product dimensions (WxDxH): 92.0 x 8.9 x 52.0
- Product weight: 0.091 kg

Tuner/Reception/Transmission

- Station presets: 20
- Tuner Bands: FM

Video Playback

- WMV9: 320 x 240, 30 fps, 512 kbps

Audio Capturing

- Built-in microphone: mono
- Voice recording
- FM radio recording

Partners

- 7digital
- Audible



Issue date 2017-03-20

Version: 2.2.6

12 NC: 8670 000 61332
EAN: 87 12581 53304 5

© 2017 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com

* Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.

* Actual transfer speed may vary based on your operating system and software configuration.

* 1 GB = 1 billion bytes; available storage capacity will be less.