




Philips GoGEAR  
MP3 player with  
FullSound™

Raga  
4 GB\*

GoGEAR



SA4RGA04KN



## Colour your world with superb sound

Small, fun and colourful

Small and fun, the Philips GoGEAR Raga MP3 player SA4RGA04KN with FullSound brings your favourites to life. Philips Songbird ensures endless music discovery and easy synchronisation, while FastCharge offers quick charging.

### Superb quality sound

- FullSound™ to bring your MP3 music to life

### Complements your life

- Soft and smooth finish for easy comfort and handling
- Full colour display for intuitive and enjoyable navigation
- Enjoy up to 15-hour music playback

### Easy and intuitive

- LikeMusic for playlists of songs that sound great together
- Quick 6-minute charge for 60 minutes of play
- Folder view to organise and view media files as you do on your PC

# PHILIPS

MP3 player  
Raga 4 GB\*

SA4RGA04KN/12

# Highlights

## Soft and smooth finish

Soft and smooth finish for easy comfort and handling

## Full colour display

Full colour display for intuitive and enjoyable navigation

## Up to 15-hour music playback



Enjoy up to 15-hour music playback

## LikeMusic



LikeMusic lets you experience more of the music that you like most — with just a click! No need to sort through your music library or wait for serendipity to strike. LikeMusic is a Philips patented algorithm that analyses songs in your library to identify similar music characteristics. These characteristics help LikeMusic create smart playlists of songs that simply sound great together. Just click on a song that you like and hit the LikeMusic icon — a playlist will instantly appear. Give it a name


and enjoy your new playlist—or rediscover songs—on your PC or your GoGear player.

## Fast charging (60 mins)



Sometimes, you just need your GoGEAR player to take you from home to office and back again, or for a short run—but you forgot to charge it last night. Say goodbye to frustration and boring, silent journeys, with Fast Charge. Philips' smart and convenient solution lets you plug your GoGEAR into your PC or USB charger for just 6 minutes and in return, you get a whopping 60 minutes of audio playback! Fast Charge works by relying on much higher current levels to give your lithium-ion battery the power it needs to tide you over in a jiffy...and keep the music going.

## Folder view



Folder view is an optional directory view of the GoGear player that lets you view all the files on your player as if it were a computer. Once

you select Folder view, opening any supported file (i.e. music, pictures or videos) is as easy as selecting the file and hitting Play.

## FullSound™



Philips' innovative FullSound technology faithfully restores sonic details to compressed MP3 music, dramatically enriching and enhancing it, so you can experience CD music without any distortion. Based on an audio post-processing algorithm, FullSound combines Philips' renowned expertise in music reproduction with the power of the latest generation Digital Signal Processor (DSP). The result is fuller bass with more depth and impact, boosted voice and instrument clarity, and rich detail. Rediscover your compressed MP3 music in true-to-life sound that will touch your soul and move your feet.



# Specifications

## Picture/Display

- Backlight
- Type: LCD
- Diagonal screen size (cm): 2.79
- Diagonal screen size (inch): 1.1 inch
- Resolution: 128 x 64

## Sound

- Sound Enhancement: FullSound
- Equalizer customisable
- Equalizer settings: Balanced, Powerful, Warm, Clear, Bright
- Channel separation: 45 dB
- Frequency response: 80 - 18 k Hz
- Output power (RMS): 2 x 2.5 mW
- Signal to noise ratio: >84 dB

## Audio Playback

- Compression format: MP3, WAV, WMA
- ID3 Tag support: Song title, artist, album
- MP3 bit rates: 8-320 bps and VBR
- MP3 sample rates: 8, 11.025, 16, 22.050, 32, 48 kHz
- WMA bit rates: 5-320 kbps
- WMA sample rates: 8, 11.025, 16, 22.050, 32, 44.1, 48 kHz
- Digital Rights Management: No

## Video Playback

- N/A

## Still Picture Playback

- N/A

## Tuner/Reception/Transmission

- No

## Storage Media

- Built-in memory type: NAND Flash
- Built-in memory (RAM): 4 GB
- Music memory capacity, MP3: Up to 900 tracks\*
- Mass storage class compliant
- Mass Trans. Protocol Compliant: No

## Connectivity

- Headphones: 3.5 mm
- USB: USB 2.0

## Convenience

- Keypad lock: Yes, option key
- Superscroll: No
- Firmware upgradeable: Yes, via SongBird
- Battery charging indication: On user interface
- Charge and play: when connected to a PC
- Customisable volume limit
- Dedicated volume controls: No
- Volume control

## Accessories

- Headphones
- Quick start guide
- USB cable

## Green Specifications

- Lead-free soldered product

## System Requirements

- USB: Free USB port
- Internet connection: Yes (for access to updated support documents, manuals, future firmware and PC software upgrades)
- PC OS: Windows XP (SP3)/Windows Vista/Windows 7

## Power

- Battery Type: LI-Polymer
- Rechargeable: Yes, via USB
- Battery capacity: 220 mAh
- Play time on internal battery: Up to 15 hours music playback

## Dimensions

- Packaging type: D-box
- D-box dimensions (WxDxH): 90 x 30 x 90 mm
- Product dimensions (WxDxH): 49.9 x 12.9 x 43.4 mm
- Product weight: 0.022 kg

## Software

- Philips Songbird

## Partners

- 7digital



Issue date 2016-10-25

Version: 4.0.6

12 NC: 8670 000 87536  
EAN: 08 71258 16373 54

© 2016 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)

\* Storage capacity based on 4 minutes per song and 64 kbps WMA encoding.  
\* Storage capacity based on 4 minutes per song and 64 kbps WMA or 128 kbps MP3 encoding.  
\* Actual transfer speed may vary based on your operating system and software configuration.  
\* 1 GB = 1 billion bytes; available storage capacity will be less.  
\* Rechargeable batteries have a limited number of charge cycles and may eventually need to be replaced. Battery life and number of charge cycles vary by use and settings.