

Instructions for use
 Mode d'emploi
 Gebrauchsanleitung
 Mini case acustice IFU
 Gebruiksaanwijzing
 Mini altifalantes IFU
 Mini altavoces IFU
 Minihögtalare IFU

Instruction for use Philips speakers

1. Introduction

CONGRATULATIONS ! You have just bought a sophisticated surround sound stereo loudspeaker set. To ensure the best performance of your surround sound stereo loudspeakers, please read this document carefully.

2. Features

- PMPO 160 Watt
- 2x12m cable included
- Magnetically shielded
- Adjustable listening position
- Wall mounting
- Quick fit cable connection
- Two way bass reflex system

3. Installation

See figure 1.

4. Specifications

Frequency range	: 50..22 000 Hz
Impedance	: 8 Ω
Woofer	: 4"
Tweeter	: 2"
PMPO	: 160 W
RMS power	: 2 x 20 W
Weight	: 5.2 kg

5. Precautions

- Do not leave the speakers near heat sources. Do not expose to direct sunlight, excessive dust, moisture, rain or any kind of mechanical shock.
- Do not use alcohol, thinner or petroleum-based substances to clean the speakers.




Figure 1

