



Philips  
Headband headphones

Soft comfy cushions

SBCHP400



## Dynamic bass

at home and on the go

This slim powerful hi-fi stereo headphone provides you with a perfect listening experience at home or on the go.

### Always ready to go

- A 2m long cable that lets you put the player in your bag
- 24k gold-plated plug ensures an ultra reliable connection
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- Folds flat to fits easily in your bag

### The perfect listening experience

- 32mm speaker driver delivers high performance sound
- Hear what's going on and listen to your DJ style headphone

# PHILIPS

sense and simplicity

Headband headphones  
Soft comfy cushions

# Specifications

## Sound

- Acoustic system: closed
- Diaphragm: Mylar dome
- Magnet type: Neodymium
- Voice coil: CCAW
- Frequency response: 20 - 25 000 Hz
- Impedance: 32 ohm
- Maximum power input: 500 mW
- Sensitivity: 106 dB
- Speaker diameter: 32 mm

## Connectivity

- Cable Connection: two-sided
- Cable length: 2 m
- Connector: 3.5 & 6.3 mm
- Finishing of connector: gold-plated
- Type of cable: LC-OFC

## Accessories

- Adaptor plug: 3.5 - 6.3 mm

## Packaging dimensions

- Packaging dimensions (W x H x D):

- 19.8 x 24.9 x 7.5 cm
- Gross weight: 0.29 kg
- Nett weight: 0.142 kg
- Tare weight: 0.148 kg
- EAN: 87 10895 80489 9
- Number of products included: 1
- Packaging type: Blister

## Outer Carton

- Gross weight: 9.862 kg
- Outer carton (L x W x H): 47.5 x 46 x 57 cm
- Nett weight: 3.408 kg
- Tare weight: 6.454 kg
- EAN: 87 10895 81618 2
- Number of consumer packagings: 24

## Inner Carton

- Gross weight: 2.148 kg
- Inner carton (L x W x H): 46 x 22.2 x 28.3 cm
- Nett weight: 0.852 kg
- Tare weight: 1.296 kg
- EAN: 87 10895 81617 5
- Number of consumer packagings: 6

SBCHP400/00

# Highlights

## 32 mm speaker driver

The 32 mm speaker driver is a compact yet powerful element for delivering non-distorted sound with any given input power.

## DJ monitoring style

It is a reversible ear-shell for listening with one ear

## 2m cable

The ideal length of cable to give you more freedom of movement and to choose where you carry your audio device.

## 24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

## Flat foldable

A convenient folding mechanism means the earshell folds flat for compact storage in your pocket or bag.



Issue date 2013-02-01

Version: 8.0.11

12 NC: 9082 100 02555  
EAN: 87 10895 80489 9

© 2013 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)