



Philips
Headband headphones

SBCHP430



Full bodied sound anywhere

at home and on the go

A powerful HiFi stereo headphone with an in-cord volume control and extension cable for the perfect listening experience everywhere where.

Always ready

- A 1.2m long cable that is ideal for outdoor use
- A 1.8 m long extension cable for more freedom of movement
- 24k gold-plated adaptor for ultra reliable connection
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- Folds flat to fits easily in your bag
- In-line control that simplifies volume adjustment

The perfect listening experience

- 32mm speaker driver delivers high performance sound
- Hear what's going on and listen to your DJ style headphone

PHILIPS

Specifications

Sound

- Diaphragm: Mylar dome
- Acoustic system: Closed
- Magnet type: Neodymium
- Voice coil: CCAW
- Frequency response: 20 - 25 000 Hz
- Impedance: 32 Ohm
- Maximum power input: 500 mW
- Sensitivity: 106 dB
- Speaker diameter: 32

Connectivity

- Cable Connection: Two-sided
- Cable length: 1.2 m + 1.8 m
- Connector: 3.5 & 6.3 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: LC-OFC

Convenience

- Volume control

Accessories

- Adaptor plug: 3.5-6.3 mm

Inner Carton

- Gross weight: 1.08 kg
- Inner carton (L x W x H): 22.5 x 20.6 x 26 cm
- Nett weight: 0.459 kg
- Tare weight: 0.621 kg
- EAN: 87 10895 82460 6
- Number of consumer packagings: 3

Outer Carton

- Gross weight: 9.9 kg
- Outer carton (L x W x H): 47 x 43.2 x 54.6 cm
- Nett weight: 3.672 kg
- Tare weight: 6.228 kg
- EAN: 87 10895 82461 3
- Number of consumer packagings: 24

Packaging dimensions

- Packaging dimensions (W x H x D): 19.9 x 253 x 7.6 cm
- Gross weight: 0.309 kg
- Nett weight: 0.153 kg
- Tare weight: 0.156 kg
- EAN: 87 10895 82459 0
- Number of products included: 1
- Packaging type: Blister

Highlights

32 mm speaker driver

The 32 mm speaker driver is a compact yet powerful element for delivering non-distorted sound with any given input power.

DJ monitoring style

It is a reversible ear-shell for listening with one ear

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

1.8 m extension cable

Give yourself more freedom of movement with an extension cable fitted with a standard 3.5 mm socket on one end and a standard 3.5 mm plug on the other.

24k Gold-plated adaptor

Be assured of a perfect connection and high-quality sound regardless of whether your audio devices are fitted with 3.5 or 6.35 mm jack sockets.

Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

Flat foldable

A convenient folding mechanism means the earshell folds flat for compact storage in your pocket or bag.

In-line volume control

Adjust the volume to your preferred level without having to go to the audio source unit.

