



Philips
Headband headphones

SBCHP460



Superb Bass

HiFi sound anywhere!

A fold-up headphone for truly hassle-free listening whether you're at home or outside

The perfect listening experience

- 40mm speaker driver delivers sound without distortion
- Hear what's going on and listen to your DJ style headphone

Always ready

- A 1.2m long cable that is ideal for outdoor use
- A 1.8 m long extension cable for more freedom of movement
- 24k gold-plated adaptor for ultra reliable connection
- 3.5 - 6.35mm adaptor connects to all types of audio devices
- Foldable headband makes headphone easy to carry around
- In-line control that simplifies volume adjustment

PHILIPS

Specifications

Sound

- Frequency response: 15 - 28 000 Hz
- Acoustic system: closed, open
- Magnet type: Neodymium
- Voice coil: CCAW
- Impedance: 32 ohm
- Maximum power input: 500 mW
- Sensitivity: 106 dB
- Speaker diameter: 40 mm
- Diaphragm: Mylar dome

Connectivity

- Connector: 3.5 & 6.3 mm
- Finishing of connector: gold-plated
- Cable length: 1.2 m + 1.8 m
- Type of cable: LC-OFC
- Cable Connection: two-sided

Convenience

- Volume control

Accessories

- Adaptor plug: 3.5 - 6.3 mm

Outer Carton

- Gross weight: 12.4103 kg
- Outer carton (L x W x H): 53 x 42.5 x 56 cm
- Nett weight: 5.0832 kg
- Tare weight: 7.3271 kg
- EAN: 87 12581 52452 4
- Number of consumer packagings: 24

Packaging dimensions

- Packaging dimensions (W x H x D): 19.8 x 24.9 x 8.3 cm
- Gross weight: 0.3907 kg
- Nett weight: 0.2118 kg
- Tare weight: 0.1789 kg
- EAN: 87 10895 80492 9
- Number of products included: 1
- Packaging type: Blister

Inner Carton

- EAN: 87 12581 52475 3
- Gross weight: 1.1014 kg
- Inner carton (L x W x H): 25.8 x 20.5 x 27 cm
- Nett weight: 0.6354 kg
- Number of consumer packagings: 3
- Tare weight: 0.466 kg

Highlights

40 mm speaker driver

The 40 mm speaker driver is made of a composite mylar material for a highly sensitive yet powerful element that delivers sound without audible distortion.

DJ monitoring style

It is a reversible ear-shell for listening with one ear

1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

1.8 m extension cable

Give yourself more freedom of movement with an extension cable fitted with a standard 3.5 mm socket on one end and a standard 3.5 mm plug on the other.

24k Gold-plated adaptor

Be assured of a perfect connection and high-quality sound regardless of whether your audio devices are fitted with 3.5 or 6.35 mm jack sockets.

Audio jack adaptor included

With this adaptor, you can use your headphone on equipment with either 3.5 or 6.35 mm jacks, giving you a wider choice of audio devices.

Foldable headband

The headphone can fold down to a small size for convenient storage when not in use.

In-line volume control

Adjust the volume to your preferred level without having to go to the audio source unit.

