



Philips
HiFi Stereo Headphone

SBCHP890

Premium Sound

XXL 50mm neodymium speaker

Premium sound quality and ultimate comfort for the perfect listening experience

The perfect listening experience

- 50mm speaker driver for sound without audible distortion
- High quality Linear Crystal Oxygen Free Copper cable

You'll forget you're wearing them!

- Self adjusting inner headband ensures a comfortable fit
- Ultimate wearing comfort for many hours of listening

Always ready

- Detachable cable extends product life and simplifies storage
- Headphone stand provides convenience and storage
- Single-sided cable reduces tangling and improves comfort
- A 4m detachable cable for extended life & simplified storage

PHILIPS

Specifications

Sound

- Acoustic system: Open
- Frequency response: 5 - 30 000 Hz
- Impedance: 32 Ohm
- Magnet type: Neodymium
- Maximum power input: 1500 mW
- Sensitivity: 106 dB
- Speaker diameter: 50
- Voice coil: CCAW

Connectivity

- Connector: 3.5 & 6.3 mm stereo
- Finishing of connector: 24k Gold-plated
- Cable length: 4 m
- Type of cable: LC-OFC
- Cable Connection: One-sided
- Detachable cable

Accessories

- Adaptor plug: 3.5-6.3 mm

Highlights

50 mm speaker driver

The 50 mm speaker driver combines the sensitivity of composite Mylar material with the power of neodymium for the magnetic circuit to deliver powerful, distortion-free sound.

LC-OFC cable

The extremely pure copper used for this cable minimizes transmission losses and delivers superb signal quality to the headphone, and pure sound to your ears.

Self adjusting inner headband

The inner headband of these Philips headphones makes it easy to obtain a perfect fit for your head. The mechanism adjusts automatically for comfort.

Ultimate wearing comfort

The soft velvet ear cushions and ergonomically-shaped ear shells enhance comfort for your prolonged audio enjoyment.

Detachable cable

A detachable cable is both convenient to store and easy to replace, so there is no need to buy a new headphone if the cable ever breaks.

Headphone stand

Simply hang up your headphone when you do not use it.

Single-sided cable

The cable is conveniently connected to just one side, considerably reducing the risk of tangling and simplifying winding the cable up for storage.

4m cable

A detachable cable is convenient to connect or store away depending on your needs.



Issue date 2014-02-05

Version: 1.0.2

12 NC: 9082 100 00464
EAN: 87 10101 67525 1

© 2014 Koninklijke Philips N.V.
All Rights reserved.

Specifications are subject to change without notice.
Trademarks are the property of Koninklijke Philips N.V.
or their respective owners.

www.philips.com