



Philips  
Earclip Headphones

SBCHS480

## Music clip - music to your ears

great looks, great sounds

Elegant in-ear headphones that look as good as the perform

### **Music to your ears**

- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnets enhance bass performance and sensitivity

### **Made to fit you and your lifestyle**

- 15mm speaker driver optimizes wearing comfort
- Adjust the fit for increased wearing comfort
- Asymmetric cable keeps the cable out the way

### **Always ready to go**

- A 1.2m long cable that is ideal for outdoor use
- Benefit from the cool look and light weight of aluminium

# PHILIPS

# Specifications

## Sound

- Acoustic system: Open
- Magnet type: Neodymium
- Voice coil: CCAW
- Diaphragm: Mylar dome
- Frequency response: 10 - 22 000 Hz
- Impedance: 16 Ohm
- Maximum power input: 50 mW
- Sensitivity: 106 dB
- Speaker diameter: 15 mm
- Type: Dynamic

## Connectivity

- Cable Connection: Two-parallel, asymmetric
- Cable length: 1.2 m
- Connector: 3.5 mm stereo
- Finishing of connector: 24k Gold-plated
- Type of cable: OFC

## Packaging Data

- 12NC: 908210001677
- EAN/UPC/GTIN: 8710895759243
- Gross weight: 0.0704 kg
- Tare weight: 0.049 kg

- Length: 116 mm
- Width: 340 mm
- Height: 222 mm

## Inner Carton

- 12NC: 908210001677
- EAN/UPC/GTIN: 8710895759717
- Quantity: 6
- Gross weight: 0.5829 kg
- Tare weight: 0.1605 kg
- Length: 230 mm
- Width: 220 mm
- Height: 125 mm

## Outer Carton

- 12NC: 908210001677
- EAN/UPC/GTIN: 8710895759724
- Quantity: 48
- Gross weight: 5.8 kg
- Tare weight: 4.7 kg
- Length: 480 mm
- Width: 460 mm
- Height: 285 mm

# Highlights

## 24k Gold-plated plug

Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.

## CCA W voice coil

By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.

## Neodymium magnets

Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.

## 15 mm speaker driver

Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.

## Adjustable earpiece

By sliding the earpiece on the arm, a precise fit with optimum comfort is easily achieved for your listening pleasure.

## Asymmetric cabling system

This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.

## 1.2m cable

The ideal cable length to give you the freedom to put your audio device where you want.

## Aluminium design

Aluminium is light, strong and has a look that complements the headphone's cool design.



Issue date 2014-02-11

Version: 2.0.3

12 NC: 9082 100 01677  
EAN: 87 10895 75924 3

© 2014 Koninklijke Philips N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips N.V.  
or their respective owners.

[www.philips.com](http://www.philips.com)