



Philips  
Earclip Headphones

SBCHS480

## Music clip - music to your ears

great looks, great sounds

Elegant in-ear headphones that look as good as the perform

### **Music to your ears**

- 24k gold-plated plug ensures an ultra reliable connection
- Copper Cladded Aluminium Wire improves sound quality
- Neodymium magnet enhances bass performance and sensitivity

### **Made to fit you and your lifestyle**

- 15mm speaker driver optimizes wearing comfort
- Adjust the fit for increased wearing comfort
- Asymmetric cable keeps the cable out the way

### **Always ready to go**

- A 1.2m long cable that is ideal for outdoor use
- Benefit from the cool look and light weight of aluminium

# PHILIPS

## Technical specifications

### Sound

- **Acoustic system:** Open
- **Frequency response:** 10 - 22 000 Hz
- **Impedance:** 16 Ohm
- **Magnet type:** Neodymium
- **Maximum power input:** 50 mW
- **Sensitivity:** 106 dB
- **Speaker diameter:** 15 mm
- **Type:** Dynamic

- **Voice coil:** CCAW
- **Diaphragm:** Mylar dome

### Connectivity

- **Connector:** 3.5 mm stereo
- **Finishing of connector:** 24k Gold-plated
- **Cable length:** 1.2 m
- **Type of cable:** OFC
- **Cable Connection:** Two-parallel, asymmetric

## Product highlights

### 1.2 meter cable

*The ideal cable length to give you the freedom to put your audio device where you want.*

### 15 mm speaker driver

*Small enough for optimum wearing comfort and big enough to deliver crisp, non-distorted sound, the 15 mm speaker driver is an ideal size for listening enjoyment.*

### 24k Gold-plated plug

*Rest assured that the precious metal gold finishing on the plug will give you a more reliable connection for better quality audio.*

### Adjustable earpiece

*By sliding the earpiece on the arm, a precise fit with optimum comfort is easily achieved for your listening pleasure.*

### Aluminium design

*Aluminium is light, strong and has a look that complements the headphone's cool design.*

### Asymmetric cabling system

*This simple yet highly effective solution to cable tangling works effectively by enabling you to hang the cable behind your neck instead of under your chin.*

### CCA W voice coil

*By using top-quality Copper Cladded Aluminium Wire (CCA W) in the headphone driver's voice coil, the sound quality is considerably improved.*

### Neodymium magnet

*Neodymium is the best material for producing a strong magnetic field for greater sensitivity in a voice coil, better bass response and higher overall sound quality.*



Date of issue 2006-07-07

Version: 1.0

12 NC: 9082 100 01677  
EAN: 87 10895 75924 3

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips Electronics N.V. or their respective owners.  
© 2006 Koninklijke Philips Electronics N.V.  
All Rights reserved.  
[www.philips.com](http://www.philips.com)